

Achromatic Waveplates (Retarders)





- Multiple Wavelength Ranges Available
- Flat Response Over Each Broad Spectral Range
- $\lambda/4$ and $\lambda/2$ Retardance
- Mounted in Black Anodized Aluminum Housing



Common Specifications




Physical & Mechanical Properties				
Dimensional Tolerance (mm):		+0/-0.25	Construction: Crystalline	
Housing Tolerance (mm):		+0/-0.25		
Optical Properties				
Substrate:		Crystal Quartz and MgF ₂		

Technical Information




25.4mm Diameter Waveplates





30.0mm Diameter Waveplates



Products

Retardance	Wavelength Range (nm)	CA (mm)	Dia. (mm)	Type	Surface Quality	Stock Number	Price	Buy
$\lambda/4$	465 - 610	11.5	25.40	Achromatic Waveplate	20-10	#46-558	£818.59 Volume Pricing	2 In Stock
$\lambda/2$	465 - 610	11.5	25.40	Achromatic Waveplate	20-10	#46-559	£818.59 Volume Pricing	5 In Stock
$\lambda/4$	610 - 850	11.5	25.40	Achromatic Waveplate	20-10	#63-935	£818.59 Volume Pricing	Contact Us
$\lambda/2$	610 - 850	11.5	25.40	Achromatic Waveplate	20-10	#63-936	£818.59 Volume Pricing	Contact Us
$\lambda/4$	700 - 1000	11.5	25.40	Achromatic Waveplate	20-10	#46-560	£818.59 Volume Pricing	3 In Stock
$\lambda/2$	700 - 1000	11.5	25.40	Achromatic Waveplate	20-10	#46-561	£818.59 Volume Pricing	3 In Stock
$\lambda/4$	1200 - 1650	11.5	25.40	Achromatic Waveplate	20-10	#46-562	£818.59 Volume Pricing	2 In Stock
$\lambda/2$	1200 - 1650	11.5	25.40	Achromatic Waveplate	20-10	#46-563	£818.59 Volume Pricing	2 In Stock
$\lambda/4$	465 - 610	23	30.00	Achromatic Waveplate	20-10	#48-497	£919.28 Volume Pricing	3 In Stock
$\lambda/2$	465 - 610	23	30.00	Achromatic Waveplate	20-10	#48-498	£919.28 Volume Pricing	3 In Stock
$\lambda/4$	610 - 850	23	30.00	Achromatic Waveplate	20-10	#65-919	£919.28 Volume Pricing	5 In Stock
$\lambda/2$	610 - 850	23	30.00	Achromatic Waveplate	20-10	#65-920	£919.28 Volume Pricing	4 In Stock
$\lambda/4$	700 - 1000	23	30.00	Achromatic Waveplate	20-10	#48-499	£919.28 Volume Pricing	5 In Stock
$\lambda/2$	700 - 1000	23	30.00	Achromatic Waveplate	20-10	#48-500	£919.28 Volume Pricing	4 In Stock
$\lambda/4$	1200 - 1650	23	30.00	Achromatic Waveplate	20-10	#48-501	£919.28 Volume Pricing	3 In Stock
$\lambda/2$	1200 - 1650	23	30.00	Achromatic Waveplate	20-10	#48-502	£919.28 Volume Pricing	1 In Stock
$\lambda/4$	340 - 560	>8.0	12.70	Achromatic Waveplate	40-20	#39-024	£696.02 Volume Pricing	3 In Stock
$\lambda/2$	340 - 560	>8.0	12.70	Achromatic Waveplate	40-20	#39-025	£696.02 Volume Pricing	Contact Us

$\lambda/4$	340 - 560	>20.0	25.40	Achromatic Waveplate	40-20	#39-026	£888.63 Volume Pricing	1 In Stock
$\lambda/2$	340 - 560	>20.0	25.40	Achromatic Waveplate	40-20	#39-027	£888.63 Volume Pricing	1 In Stock
$\lambda/4$	340 - 560	>27.0	50.80	Achromatic Waveplate	40-20	#39-028	£2,814.73 Volume Pricing	Contact Us
$\lambda/2$	340 - 560	>34.0	50.80	Achromatic Waveplate	40-20	#39-029	£2,814.73 Volume Pricing	Contact Us
$\lambda/4$	450 - 650	>8.0	12.70	Achromatic Waveplate	40-20	#39-030	£696.02 Volume Pricing	Contact Us
$\lambda/2$	450 - 650	>8.0	12.70	Achromatic Waveplate	40-20	#39-031	£696.02 Volume Pricing	Contact Us
$\lambda/4$	450 - 650	>20.0	25.40	Achromatic Waveplate	40-20	#39-032	£888.63 Volume Pricing	5 In Stock
$\lambda/2$	450 - 650	>20.0	25.40	Achromatic Waveplate	40-20	#39-033	£888.63 Volume Pricing	Contact Us
$\lambda/4$	450 - 650	>34.0	50.80	Achromatic Waveplate	40-20	#39-034	£2,814.73 Volume Pricing	Contact Us
$\lambda/2$	450 - 650	>34.0	50.80	Achromatic Waveplate	40-20	#39-035	£2,814.73 Volume Pricing	Contact Us
$\lambda/4$	550 - 750	>8.0	12.70	Achromatic Waveplate	40-20	#39-036	£696.02 Volume Pricing	Contact Us
$\lambda/2$	550 - 750	>8.0	12.70	Achromatic Waveplate	40-20	#39-037	£696.02 Volume Pricing	1 In Stock
$\lambda/4$	550 - 750	>20.0	25.40	Achromatic Waveplate	40-20	#39-038	£888.63 Volume Pricing	2 In Stock
$\lambda/2$	550 - 750	>20.0	25.40	Achromatic Waveplate	40-20	#39-039	£888.63 Volume Pricing	1 In Stock
$\lambda/4$	550 - 750	>34.0	50.80	Achromatic Waveplate	40-20	#39-040	£2,814.73 Volume Pricing	1 In Stock
$\lambda/2$	550 - 750	>34.0	50.80	Achromatic Waveplate	40-20	#39-041	£2,814.73 Volume Pricing	Contact Us
$\lambda/4$	650 - 1100	>8.0	12.70	Achromatic Waveplate	40-20	#39-042	£696.02 Volume Pricing	2 In Stock
$\lambda/2$	650 - 1100	>8.0	12.70	Achromatic Waveplate	40-20	#39-043	£696.02 Volume Pricing	3 In Stock
$\lambda/4$	650 - 1100	>20.0	25.40	Achromatic Waveplate	40-20	#39-044	£888.63 Volume Pricing	Contact Us
$\lambda/2$	650 - 1100	>20.0	25.40	Achromatic Waveplate	40-20	#39-045	£888.63 Volume Pricing	2 In Stock

$\lambda/4$	650 - 1100	>34.0	50.80	Achromatic Waveplate	40-20	#39-046	£2,814.73 Volume Pricing	Contact Us
$\lambda/2$	650 - 1100	>34.0	50.80	Achromatic Waveplate	40-20	#39-047	£2,814.73 Volume Pricing	Contact Us
$\lambda/4$	900 - 2100	>8.0	12.70	Achromatic Waveplate	40-20	#39-048	£696.02 Volume Pricing	Contact Us
$\lambda/2$	900 - 2100	>8.0	12.70	Achromatic Waveplate	40-20	#39-049	£696.02 Volume Pricing	2 In Stock
$\lambda/4$	900 - 2100	>20.0	25.40	Achromatic Waveplate	40-20	#39-050	£888.63 Volume Pricing	1 In Stock
$\lambda/2$	900 - 2100	>20.0	25.40	Achromatic Waveplate	40-20	#39-051	£888.63 Volume Pricing	Contact Us
$\lambda/4$	900 - 2100	>34.0	50.80	Achromatic Waveplate	40-20	#39-052	£2,814.73 Volume Pricing	1 In Stock
$\lambda/2$	900 - 2100	>34.0	50.80	Achromatic Waveplate	40-20	#39-053	£2,814.73 Volume Pricing	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com