

[All Products](#) / [Microscopy](#) / [Reflective Objectives](#)

TECHSPEC® ReflX™ Objectives



- Industry Leading 19 to 31mm Working Distance
- EO Designed and Manufactured for Focusing or Imaging Applications
- Actively Aligned for Optimal Performance
- Ultra-Wide Spectral Band from 190nm to 11µm with No Chromatic Aberration
- [TECHSPEC® High Performance ReflX™ Objectives](#) Available

Common Specifications

General

Manufacturer: Edmund Optics®


Optical Properties

Transmitted Wavefront, RMS: $\lambda/10$


Threading & Mounting

Mounting Threads: RMS


Technical Information



20X ReflX™ Objectives



10X ReflX™ Objectives



Products

Style	Magnification	Coating	NA	Stock Number	Price	Buy
Infinity Corrected	10X	DUV Enhanced Aluminum (150-11000nm)	0.22	#89-722	£1,708.50 Volume Pricing	5 In Stock
Finite Conjugate	10X	DUV Enhanced Aluminum (150-11000nm)	0.23	#89-723	£1,708.50 Volume Pricing	7 In Stock
Infinity Corrected	10X	Enhanced Aluminum (200-11000nm)	0.22	#89-724	£1,708.50 Volume Pricing	4 In Stock
Finite Conjugate	10X	Enhanced Aluminum (200-11000nm)	0.23	#89-725	£1,708.50 Volume Pricing	8 In Stock
Infinity Corrected	10X	Ultrafast-Enhanced Silver	0.22	#13-408	£1,797.75 Volume Pricing	2 In Stock
Finite Conjugate	10X	Ultrafast-Enhanced Silver	0.23	#13-409	£1,797.75 Volume Pricing	1 In Stock
Infinity Corrected	10X	Protected Gold (700-11000nm)	0.22	#89-726	£1,797.75 Volume Pricing	1 In Stock
Finite Conjugate	10X	Protected Gold (700-11000nm)	0.23	#89-727	£1,797.75 Volume Pricing	Contact Us
Infinity Corrected	15X	DUV Enhanced Aluminum (150-11000nm)	0.28	#59-315	£1,895.50 Volume Pricing	2 In Stock
Finite Conjugate	15X	DUV Enhanced Aluminum (150-11000nm)	0.28	#59-316	£1,895.50 Volume Pricing	Contact Us
Infinity Corrected	15X	Enhanced Aluminum (200-11000nm)	0.28	#58-417	£1,895.50 Volume Pricing	2 In Stock
Finite Conjugate	15X	Enhanced Aluminum (200-11000nm)	0.28	#58-421	£1,895.50 Volume Pricing	Contact Us
Infinity Corrected	15X	Ultrafast-Enhanced Silver	0.28	#13-410	£1,989.00 Volume Pricing	2 In Stock
Finite Conjugate	15X	Ultrafast-Enhanced Silver	0.28	#13-411	£1,989.00 Volume Pricing	1 In Stock

Infinity Corrected	15X	Protected Gold (700-11000nm)	0.28	#58-418	£1,989.00 Volume Pricing	4 In Stock
Finite Conjugate	15X	Protected Gold (700-11000nm)	0.28	#58-422	£1,989.00 Volume Pricing	Contact Us
Infinity Corrected	20X	DUV Enhanced Aluminum (150-11000nm)	0.33	#39-141	£1,895.50 Volume Pricing	3 In Stock
Finite Conjugate	20X	DUV Enhanced Aluminum (150-11000nm)	0.33	#39-145	£1,895.50 Volume Pricing	4 In Stock
Infinity Corrected	20X	Enhanced Aluminum (200-11000nm)	0.33	#39-142	£1,895.50 Volume Pricing	Contact Us
Finite Conjugate	20X	Enhanced Aluminum (200-11000nm)	0.33	#39-146	£1,895.50 Volume Pricing	1 In Stock
Finite Conjugate	20X	Ultrafast-Enhanced Silver	0.33	#13-413	£1,989.00 Volume Pricing	3 In Stock
Infinity Corrected	20X	Ultrafast-Enhanced Silver	0.33	#13-412	£1,989.00 Volume Pricing	1 In Stock
Infinity Corrected	20X	Protected Gold (700-11000nm)	0.33	#39-143	£1,989.00 Volume Pricing	2 In Stock
Finite Conjugate	20X	Protected Gold (700-11000nm)	0.33	#39-147	£1,989.00 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com