

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Optical Diffusers](#)

Ground Glass Diffusers



- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Common Specifications

General

Note:

Sandblasted on first surface

Physical & Mechanical Properties

Thickness (mm): 1.60


Optical Properties

Coating: Uncoated

Substrate: Float Glass

Wavelength Range (nm): 350 - 2000

Technical Information



Products

Dia. (mm)	Coating	Dimensions (mm)	Grit	Thickness (mm)	Stock Number	Price	Buy
5.00	Uncoated	-	120	1.60	#83-416	£17.20 Volume Pricing	20+ In Stock
6.00	Uncoated	-	120	1.60	#83-081	£17.20 Volume Pricing	20+ In Stock
10.00	Uncoated	-	120	1.60	#83-082	£17.20 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	120	1.60	#83-083	£17.20 Volume Pricing	20+ In Stock
12.50	Uncoated	-	120	1.60	#83-418	£11.40 Volume Pricing	10 In Stock
-	Uncoated	12.50 x 12.50	120	1.60	#83-084	£17.20 Volume Pricing	20+ In Stock
15.00	Uncoated	-	120	1.60	#83-379	£19.20 Volume Pricing	20+ In Stock
20.00	Uncoated	-	120	1.60	#83-380	£19.20 Volume Pricing	20+ In Stock
25.00	Uncoated	-	120	1.60	#83-419	£12.40 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	120	1.60	#83-381	£19.20 Volume Pricing	2 In Stock
50.00	Uncoated	-	120	1.60	#83-420	£16.20 Volume Pricing	20+ In Stock
-	Uncoated	50.00 x 50.00	120	1.60	#83-382	£22.80 Volume Pricing	20+ In Stock
100.00	Uncoated	-	120	1.60	#83-383	£54.00 Volume Pricing	7 In Stock
-	Uncoated	100.00 x 100.00	120	1.60	#83-384	£42.00 Volume Pricing	20+ In Stock
-	Uncoated	150.00 x 150.00	120	1.60	#83-385	£58.80 Volume Pricing	3 In Stock
-	Uncoated	200.00 x 200.00	120	1.60	#83-386	£68.80 Volume Pricing	6 In Stock
-	Uncoated	250.00 x 250.00	120	1.60	#83-387	£89.60 Volume Pricing	20+ In Stock

5.00	Uncoated	-	220	1.60	#62-614	£16.80 Volume Pricing	20+ In Stock
6.00	Uncoated	-	220	1.60	#45-650	£17.20 Volume Pricing	20+ In Stock
10.00	Uncoated	-	220	1.60	#45-651	£16.80 Volume Pricing	20+ In Stock
-	Uncoated	10.00 x 10.00	220	1.60	#62-615	£17.20 Volume Pricing	20+ In Stock
12.50	Uncoated	-	220	1.60	#62-616	£11.40 Volume Pricing	20+ In Stock
-	Uncoated	12.50 x 12.50	220	1.60	#62-617	£17.20 Volume Pricing	20+ In Stock
15.00	Uncoated	-	220	1.60	#45-652	£19.20 Volume Pricing	20+ In Stock
20.00	Uncoated	-	220	1.60	#62-618	£19.20 Volume Pricing	Contact Us
25.00	Uncoated	-	220	1.60	#45-653	£13.80 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	220	1.60	#45-654	£19.20 Volume Pricing	20+ In Stock
50.00	Uncoated	-	220	1.60	#62-619	£16.60 Volume Pricing	20+ In Stock
-	Uncoated	50.00 x 50.00	220	1.60	#45-655	£22.80 Volume Pricing	20+ In Stock
100.00	Uncoated	-	220	1.60	#62-620	£56.40 Volume Pricing	20+ In Stock
-	Uncoated	100.00 x 100.00	220	1.60	#45-656	£42.00 Volume Pricing	6 In Stock
-	Uncoated	150.00 x 150.00	220	1.60	#47-951	£58.80 Volume Pricing	12 In Stock
-	Uncoated	200.00 x 200.00	220	1.60	#47-952	£67.60 Volume Pricing	20+ In Stock
-	Uncoated	250.00 x 250.00	220	1.60	#47-953	£88.00 Volume Pricing	20+ In Stock
10.00	Uncoated	-	600	1.60	#38-782	£17.20 Volume Pricing	15 In Stock
-	Uncoated	10.00 x 10.00	600	1.60	#38-783	£17.20 Volume Pricing	11 In Stock
12.50	Uncoated	-	600	1.60	#38-784	£11.40 Volume Pricing	20+ In Stock

-	Uncoated	12.50 x 12.50	600	1.60	#38-785	£17.20 Volume Pricing	13 In Stock
25.00	Uncoated	-	600	1.60	#38-786	£13.80 Volume Pricing	20+ In Stock
-	Uncoated	25.00 x 25.00	600	1.60	#38-787	£19.80 Volume Pricing	5 In Stock
50.00	Uncoated	-	600	1.60	#38-788	£16.60 Volume Pricing	4 In Stock
-	Uncoated	50.00 x 50.00	600	1.60	#38-789	£22.80 Volume Pricing	20+ In Stock
100.00	Uncoated	-	600	1.60	#38-790	£54.00 Volume Pricing	20+ In Stock
-	Uncoated	100.00 x 100.00	600	1.60	#38-791	£43.20 Volume Pricing	7 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com