

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Specialty Lenses](#)

Gradient Index (GRIN) Rod Lenses




- Ideal for Fiber Coupling and Laser Diode Applications
- Comparable Performance to Conventional Aspherical Singlets
- Multiple Sizes and Wavelength Options
- [GRIN Lens Grippers and Table Mounts](#) Available

Common Specifications

Physical & Mechanical Properties			
Clear Aperture (%):		90.00	Length Tolerance (%): ±5
Optical Properties			
Substrate:		Aluminosilicate Glass Embedded with Silver Ions	Surface Quality: 40-20
Working Distance Tolerance (mm):		±0.02	

Technical Information



Products

Dia. (mm)	Substrate	Type	Coating	EFL (mm)	NA	Stock Number	Price	Buy
0.35	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.30	0.55	#88-355	£73.20 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.54	#64-515	£51.60 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.88	0.54	#64-517	£51.60 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.67	0.52	#64-519	£51.60 Volume Pricing	20+ In Stock
#64-520 Clearance								
								
Clearance								
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.								
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.52		£51.60 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.45	0.53	#64-521	£51.60 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.89	0.54	#64-523	£51.60 Volume Pricing	20+ In Stock

1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-524	£51.60 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.68	0.52	#64-525	£51.60 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.70	0.51	#64-526	£51.60 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.46	0.52	#64-527	£51.60 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	0.90	0.53	#64-529	£51.60 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	Uncoated	1.71	0.51	#64-531	£51.60 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.45	0.54	#64-533	£61.20 Volume Pricing	20+ In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	0.88	0.54	#64-535	£61.20 Volume Pricing	Contact Us
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.67	0.52	#64-537	£61.20 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (450- 700nm)	1.69	0.52	#64-538	£61.20 Volume Pricing	Contact Us
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.45	0.53	#64-539	£61.20 Volume Pricing	8 In Stock
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	0.89	0.54	#64-541	£61.20 Volume Pricing	20+ In Stock

1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.68	0.52	#64-543	£61.20 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (800- 1000nm)	1.70	0.51	#64-544	£61.20 Volume Pricing	20+ In Stock
0.50	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.46	0.52	#64-545	£61.20 Volume Pricing	Contact Us
1.00	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	0.90	0.53	#64-547	£61.20 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.71	0.51	#64-549	£61.20 Volume Pricing	20+ In Stock
1.80	Aluminosilicate Glass Embedded with Silver Ions	Gradient Index Lens	BBAR (1310- 1550nm)	1.72	0.51	#64-550	£61.20 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com