

[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Plate Beamsplitters](#)

Plate Beamsplitters



- Low-Cost Design
- Multiple Sizes Available
- Many Beamsplitting Ratios Available

Common Specifications




Physical & Mechanical Properties


Clear Aperture (%):	>85	Construction:	Plate
Dimensional Tolerance (mm):	±0.38	Edges:	Cut

Optical Properties

Substrate:	Float Glass	Surface Flatness (P-V):	4 - 6λ
Surface Quality:	80-50	Wavelength Range (nm):	400 - 700

Technical Information





Products

Dia. (mm)	Dimensions (mm)	Substrate	Reflection/Transmission Ratio (R/T)	Wavelength Range (nm)	Thickness (mm)	Stock Number	Price	Buy
-	12.0 x 19.0	Float Glass	10/90	400 - 700	1.00	#31-416	£32.18 Volume Pricing	20+ In Stock
12.50	-	Float Glass	25/75	400 - 700	1.00	#46-664	£43.78 Volume Pricing	13 In Stock
12.50	-	Float Glass	30/70	400 - 700	1.00	#45-312	£43.78 Volume Pricing	20+ In Stock
12.50	-	Float Glass	40/60	400 - 700	1.00	#46-665	£43.78 Volume Pricing	20+ In Stock
12.50	-	Float Glass	50/50	400 - 700	1.00	#45-313	£43.78 Volume Pricing	20+ In Stock
12.50	-	Float Glass	70/30	400 - 700	1.00	#45-314	£43.78 Volume Pricing	11 In Stock
12.50	-	Float Glass	75/25	400 - 700	1.00	#46-666	£43.78 Volume Pricing	20+ In Stock
-	12.50 x 12.50	Float Glass	25/75	400 - 700	1.00	#13-396	£43.78 Volume Pricing	14 In Stock
-	12.50 x 12.50	Float Glass	30/70	400 - 700	1.00	#13-397	£43.78 Volume Pricing	20+ In Stock
-	12.50 x 12.50	Float Glass	50/50	400 - 700	1.00	#13-399	£43.78 Volume Pricing	2 In Stock
-	12.50 x 12.50	Float Glass	70/30	400 - 700	1.00	#13-400	£43.78 Volume Pricing	20+ In Stock
-	12.50 x 12.50	Float Glass	75/25	400 - 700	1.00	#13-401	£43.78 Volume Pricing	20+ In Stock
-	12.5 x 17.5	Float Glass	25/75	400 - 700	1.00	#46-604	£43.78 Volume Pricing	20+ In Stock
-	12.5 x 17.5	Float Glass	30/70	400 - 700	1.00	#45-315	£43.78 Volume Pricing	20+ In Stock
-	12.5 x 17.5	Float Glass	40/60	400 - 700	1.00	#46-605	£43.78 Volume Pricing	12 In Stock
-	12.5 x 17.5	Float Glass	50/50	400 - 700	1.00	#45-316	£43.78 Volume Pricing	20+ In Stock
-	12.5 x 17.5	Float Glass	70/30	400 - 700	1.00	#45-317	£43.78 Volume Pricing	20+ In Stock
-	12.5 x 17.5	Float Glass	75/25	400 - 700	1.00	#46-606	£43.78 Volume Pricing	20+ In Stock
-	18.0 x 30.0	Float Glass	25/75	400 - 700	2.00	#46-687	£43.78 Volume Pricing	3 In Stock
-	18.0 x 30.0	Float Glass	30/70	400 - 700	2.00	#46-688	£43.78 Volume Pricing	5 In Stock
-	18.0 x 30.0	Float Glass	40/60	400 - 700	2.00	#46-689	£43.78 Volume Pricing	20+ In Stock
-	18.0 x 30.0	Float Glass	50/50	400 - 700	2.00	#31-414	£43.78 Volume Pricing	20+ In Stock

-	18.0 x 30.0	Float Glass	70/30	400 - 700	2.00	#46-690	£43.78 Volume Pricing	2 In Stock
-	18.0 x 30.0	Float Glass	75/25	400 - 700	2.00	#46-691	£43.78 Volume Pricing	20+ In Stock
-	20.0 x 27.0	Float Glass	25/75	400 - 700	1.00	#46-692	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 27.0	Float Glass	30/70	400 - 700	1.00	#46-693	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 27.0	Float Glass	40/60	400 - 700	1.00	#46-694	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 27.0	Float Glass	50/50	400 - 700	1.00	#32-269	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 27.0	Float Glass	70/30	400 - 700	1.00	#46-695	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 27.0	Float Glass	75/25	400 - 700	1.00	#46-696	£45.53 Volume Pricing	3 In Stock
-	20.0 x 37.0	Float Glass	25/75	400 - 700	1.00	#46-697	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 37.0	Float Glass	30/70	400 - 700	1.00	#46-698	£45.53 Volume Pricing	1 In Stock
-	20.0 x 37.0	Float Glass	40/60	400 - 700	1.00	#46-699	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 37.0	Float Glass	50/50	400 - 700	1.00	#31-413	£45.53 Volume Pricing	Contact Us
-	20.0 x 37.0	Float Glass	70/30	400 - 700	1.00	#46-700	£45.53 Volume Pricing	20+ In Stock
-	20.0 x 37.0	Float Glass	75/25	400 - 700	1.00	#46-701	£45.53 Volume Pricing	20+ In Stock
25.00	-	Float Glass	25/75	400 - 700	1.00	#43-817	£49.03 Volume Pricing	15 In Stock
25.00	-	Float Glass	30/70	400 - 700	1.00	#43-734	£49.03 Volume Pricing	20+ In Stock
25.00	-	Float Glass	40/60	400 - 700	1.00	#43-735	£49.03 Volume Pricing	7 In Stock
25.00	-	Float Glass	50/50	400 - 700	1.00	#43-736	£49.03 Volume Pricing	20+ In Stock
25.00	-	Float Glass	70/30	400 - 700	1.00	#46-607	£49.03 Volume Pricing	14 In Stock
25.00	-	Float Glass	75/25	400 - 700	1.00	#46-608	£49.03 Volume Pricing	20+ In Stock
-	25.00 x 25.00	Float Glass	25/75	400 - 700	3.00	#13-402	£50.78 Volume Pricing	6 In Stock
-	25.00 x 25.00	Float Glass	30/70	400 - 700	3.00	#13-403	£50.78 Volume Pricing	14 In Stock
-	25.00 x 25.00	Float Glass	50/50	400 - 700	3.00	#13-405	£50.78 Volume Pricing	4 In Stock
-	25.00 x 25.00	Float Glass	70/30	400 - 700	3.00	#13-406	£50.78 Volume Pricing	20+ In Stock
-	25.00 x 25.00	Float Glass	75/25	400 - 700	3.00	#13-407	£50.78 Volume Pricing	12 In Stock

-	25.0 x 38.0	Float Glass	25/75	400 - 700	3.00	#31-437	£50.78 Volume Pricing	5 In Stock
-	25.0 x 38.0	Float Glass	25/75	400 - 700	1.50	#46-702	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	30/70	400 - 700	3.00	#46-667	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	30/70	400 - 700	1.50	#46-703	£50.78 Volume Pricing	14 In Stock
-	25.0 x 38.0	Float Glass	40/60	400 - 700	3.00	#46-668	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	40/60	400 - 700	1.50	#46-704	£50.78 Volume Pricing	5 In Stock
-	25.0 x 38.0	Float Glass	50/50	400 - 700	1.50	#32-363	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	50/50	400 - 700	3.00	#31-436	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	70/30	400 - 700	3.00	#46-669	£50.78 Volume Pricing	1 In Stock
-	25.0 x 38.0	Float Glass	70/30	400 - 700	1.50	#46-705	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	75/25	400 - 700	3.00	#31-435	£50.78 Volume Pricing	20+ In Stock
-	25.0 x 38.0	Float Glass	75/25	400 - 700	1.50	#46-706	£50.78 Volume Pricing	10 In Stock
-	25.0 x 76.0	Float Glass	25/75	400 - 700	2.00	#46-670	£54.28 Volume Pricing	20+ In Stock
-	25.0 x 76.0	Float Glass	30/70	400 - 700	2.00	#46-671	£54.28 Volume Pricing	20+ In Stock
-	25.0 x 76.0	Float Glass	40/60	400 - 700	2.00	#46-672	£54.28 Volume Pricing	20+ In Stock
-	25.0 x 76.0	Float Glass	50/50	400 - 700	2.00	#31-411	£54.28 Volume Pricing	20+ In Stock
-	25.0 x 76.0	Float Glass	70/30	400 - 700	2.00	#46-673	£54.28 Volume Pricing	20+ In Stock
-	25.0 x 76.0	Float Glass	75/25	400 - 700	2.00	#46-674	£54.28 Volume Pricing	20+ In Stock
-	35.0 x 35.0	Float Glass	25/75	400 - 700	1.00	#46-609	£56.46 Volume Pricing	20+ In Stock
-	35.0 x 35.0	Float Glass	30/70	400 - 700	1.00	#45-324	£56.46 Volume Pricing	20+ In Stock
-	35.0 x 35.0	Float Glass	40/60	400 - 700	1.00	#46-610	£56.46 Volume Pricing	20+ In Stock
-	35.0 x 35.0	Float Glass	50/50	400 - 700	1.00	#45-325	£56.46 Volume Pricing	20+ In Stock
-	35.0 x 35.0	Float Glass	70/30	400 - 700	1.00	#45-326	£56.46 Volume Pricing	4 In Stock
-	35.0 x 35.0	Float Glass	75/25	400 - 700	1.00	#46-611	£56.46 Volume Pricing	9 In Stock
-	50.0 x 50.0	Float Glass	25/75	400 - 700	1.00	#43-818	£62.59 Volume Pricing	20+ In Stock

-	50.0 x 50.0	Float Glass	30/70	400 - 700	1.00	#43-360	£62.59 Volume Pricing	20+ In Stock
-	50.0 x 50.0	Float Glass	40/60	400 - 700	1.00	#43-358	£62.59 Volume Pricing	Contact Us
-	50.0 x 50.0	Float Glass	50/50	400 - 700	1.00	#43-359	£62.59 Volume Pricing	20+ In Stock
-	50.0 x 50.0	Float Glass	70/30	400 - 700	1.00	#46-612	£62.59 Volume Pricing	20+ In Stock
-	50.0 x 50.0	Float Glass	75/25	400 - 700	1.00	#46-613	£62.59 Volume Pricing	20+ In Stock
-	51.0 x 76.0	Float Glass	25/75	400 - 700	3.00	#31-434	£74.85 Volume Pricing	15 In Stock
-	51.0 x 76.0	Float Glass	30/70	400 - 700	3.00	#46-675	£74.85 Volume Pricing	14 In Stock
-	51.0 x 76.0	Float Glass	40/60	400 - 700	3.00	#46-676	£74.85 Volume Pricing	15 In Stock
-	51.0 x 76.0	Float Glass	50/50	400 - 700	3.00	#31-433	£74.85 Volume Pricing	20+ In Stock
-	51.0 x 76.0	Float Glass	70/30	400 - 700	3.00	#46-677	£74.85 Volume Pricing	8 In Stock
-	51.0 x 76.0	Float Glass	75/25	400 - 700	3.00	#31-432	£74.85 Volume Pricing	20+ In Stock
-	60.0 x 85.0	Float Glass	30/70	400 - 700	1.00	#64-407	£87.55 Volume Pricing	20+ In Stock
-	60.0 x 85.0	Float Glass	50/50	400 - 700	1.00	#64-408	£87.55 Volume Pricing	20+ In Stock
-	60.0 x 85.0	Float Glass	70/30	400 - 700	1.00	#64-409	£87.55 Volume Pricing	20+ In Stock
-	75.0 x 75.0	Float Glass	25/75	400 - 700	1.00	#46-639	£110.31 Volume Pricing	7 In Stock
-	75.0 x 75.0	Float Glass	30/70	400 - 700	1.00	#46-640	£110.31 Volume Pricing	20+ In Stock
-	75.0 x 75.0	Float Glass	40/60	400 - 700	1.00	#46-641	£110.31 Volume Pricing	20+ In Stock
-	75.0 x 75.0	Float Glass	50/50	400 - 700	1.00	#46-642	£110.31 Volume Pricing	20+ In Stock
-	75.0 x 75.0	Float Glass	70/30	400 - 700	1.00	#46-643	£110.31 Volume Pricing	13 In Stock
-	75.0 x 75.0	Float Glass	75/25	400 - 700	1.00	#46-644	£110.31 Volume Pricing	20+ In Stock
-	127.0 x 178.0	Float Glass	30/70	400 - 700	3.00	#43-362	£240.76 Volume Pricing	20+ In Stock
-	127.0 x 178.0	Float Glass	40/60	400 - 700	3.00	#61-260	£240.76 Volume Pricing	2 In Stock
-	127.0 x 178.0	Float Glass	50/50	400 - 700	3.00	#46-583	£240.76 Volume Pricing	Contact Us
-	254.0 x 356.0	Float Glass	30/70	400 - 700	3.00	#43-363	£560.32 Volume Pricing	4 In Stock
-	254.0 x 356.0	Float Glass	40/60	400 - 700	3.00	#72-502	£560.32 Volume Pricing	20+ In Stock

-	254.0 x 356.0	Float Glass	50/50	400 - 700	3.00	#46-584	£560.32 Volume Pricing	20+ In Stock
-	254.0 x 356.0	Float Glass	75/25	400 - 700	3.00	#68-268	£560.32 Volume Pricing	20+ In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com