
Family ID #2685

TECHSPEC® Germanium (Ge) Windows



- Uncoated or with AR Coatings Designed for a Variety of IR Ranges
- Minimal Chromatic Aberration Due to Low Dispersion
- Ideal for Infrared Applications Requiring Rugged Optics
- DLC Coated Germanium Windows are also Available
- Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our customer service team.
- Edmund Optics has limited remaining inventory of this part number and no raw material available to supply more once this is depleted. Please contact our Product Support Engineers to help with an alternate solution for your needs. Customer Service can provide you the latest price and availability.

Technical Information



Products

Dia. (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
5.00	1.00	Uncoated	#20-167	£436.00	20+ In Stock
10.00	0.50	Uncoated	#92-160 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	£280.00	20+ In Stock
10.00	1.50	BBAR (3000-5000nm)	#89-558	£684.00	10 In Stock
10.00	1.50	BBAR (8000-12000nm)	#47-685	£684.00	20+ In Stock

			#92-162 Clearance		
12.00	1.00	Uncoated	Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	£316.00	20+ In Stock
12.50	1.00	Uncoated	#83-341	£596.00	20+ In Stock
12.50	1.00	BBAR (3000-12000nm)	#83-347	£772.00	15 In Stock
12.50	1.00	BBAR (8000-12000nm)	#83-353	£772.00	20+ In Stock
12.50	2.00	BBAR (8000-12000nm)	#47-686	£792.00	20+ In Stock
12.50	3.00	Uncoated	#83-342	£632.00	13 In Stock
12.70	3.00	Uncoated	#74-430	£382.40	4 In Stock

			#68-736 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
20.00	2.00	Uncoated		£728.00	20+ In Stock
20.00	2.00	BBAR (3000-5000nm)	#89-562	£948.00	7 In Stock
			#64-377 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
20.00	2.00	BBAR (3000-12000nm)		£948.00	20+ In Stock

			#92-167 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
25.00	0.50	Uncoated		£420.00	20+ In Stock
25.00	2.00	BBAR (3000-5000nm)	#89-564	£1,064.00	1 In Stock
25.00	3.00	Uncoated	#68-737	£856.00	2 In Stock
25.00	3.00	BBAR (3000-5000nm)	#89-565	£1,108.00	7 In Stock
			#92-168 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
25.00	4.00	Uncoated		£480.00	20+ In Stock
25.00	5.00	Uncoated	#23-139	£908.00	16 In Stock

			#92-164 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
25.40	0.50	Uncoated		£420.00	20+ In Stock
			#92-165 New New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
25.40	1.00	Uncoated		£440.00	20+ In Stock

			#92-166 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
25.40	2.00	Uncoated		£460.00	20+ In Stock
25.40	5.00	Uncoated	#74-431	£488.00	5 In Stock
			#23-140 Clearance Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
30.00	1.00	Uncoated		£1,016.00	2 In Stock
40.00	2.00	Uncoated	#23-141	£1,524.00	Contact Us
40.00	2.00	BBAR (3000-12000nm)	#23-151	£1,984.00	5 In Stock

40.00	4.00	BBAR (3000-5000nm)	#89-567	£2,120.00	2 In Stock
50.00	1.00	BBAR (3000-5000nm)	#89-568	£2,512.00	2 In Stock
50.00	2.00	BBAR (3000-5000nm)	#89-569	£2,540.00	4 In Stock
50.00	3.00	Uncoated	#68-740	£2,008.00	Contact Us
50.00	3.00	BBAR (3000-12000nm)	#62-646	£2,612.00	1 In Stock
50.00	3.00	BBAR (8000-12000nm)	#47-688	£2,612.00	5 In Stock
76.20	5.00	BBAR (3000-5000nm)	#11-867	£5,152.00	2 In Stock

Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 Fax: 1-856-573-6295
www.edmundoptics.com