


[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Plate Beamsplitters](#)

TECHSPEC® UV Plate Beamsplitters



- Multiple Transmission/Reflection Ratios Available
- BBAR Coated Second Surface
- Fused Silica Substrate

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	>85	Construction:	Plate
Parallelism (arcmin):	<5		

Optical Properties

Angle of Incidence (°):	45		
Substrate:	Fused Silica (Corning 7980)	Surface Flatness (P-V):	1λ
Surface Quality:	60-40	Wavelength Range (nm):	250 - 450

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Substrate	Reflection/Transmission Ratio (R/T)	Wavelength Range (nm)	Thickness (mm)	Stock Number	Price	Buy
10.00	-	Fused Silica	30/70	250 - 450	1.00	#65-922	£99.81 Volume Pricing	1 In Stock
12.50	-	Fused Silica	30/70	250 - 450	2.00	#48-194	£101.56 Volume Pricing	20+ In Stock
-	12.5 x 12.5	Fused Silica	30/70	250 - 450	2.00	#48-195	£101.56 Volume Pricing	20+ In Stock
20.00	-	Fused Silica	30/70	250 - 450	2.00	#65-924	£112.94 Volume Pricing	16 In Stock
25.00	-	Fused Silica	30/70	250 - 450	2.00	#48-196	£122.57 Volume Pricing	9 In Stock
-	25.0 x 25.0	Fused Silica	30/70	250 - 450	2.00	#48-197	£122.57 Volume Pricing	15 In Stock
30.00	-	Fused Silica	30/70	250 - 450	3.00	#65-926	£140.96 Volume Pricing	5 In Stock
40.00	-	Fused Silica	30/70	250 - 450	4.00	#65-928	£182.98 Volume Pricing	11 In Stock
50.00	-	Fused Silica	30/70	250 - 450	4.00	#48-198	£203.99 Volume Pricing	12 In Stock
-	50.0 x 50.0	Fused Silica	30/70	250 - 450	4.00	#48-199	£203.99 Volume Pricing	12 In Stock
10.00	-	Fused Silica	50/50	250 - 450	1.00	#65-921	£99.81 Volume Pricing	20+ In Stock
12.50	-	Fused Silica	50/50	250 - 450	2.00	#48-188	£101.56 Volume Pricing	13 In Stock
-	12.5 x 12.5	Fused Silica	50/50	250 - 450	2.00	#48-189	£101.56 Volume Pricing	17 In Stock
#72-249 New								
								
New								
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
-	12.50 x 17.50	Fused Silica	50/50	250 - 450	2.00		£106.81 Volume Pricing	4 In Stock
20.00	-	Fused Silica	50/50	250 - 450	2.00	#65-923	£112.94 Volume Pricing	16 In Stock

25.00	-	Fused Silica	50/50	250 - 450	2.00	#48-190	£122.57 Volume Pricing	Contact Us
-	25.0 x 25.0	Fused Silica	50/50	250 - 450	2.00	#48-191	£122.57 Volume Pricing	5 In Stock
#72-250 New								
						 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
-	25.00 x 35.00	Fused Silica	50/50	250 - 450	3.00		£134.83 Volume Pricing	Contact Us
30.00	-	Fused Silica	50/50	250 - 450	3.00	#65-925	£140.96 Volume Pricing	8 In Stock
40.00	-	Fused Silica	50/50	250 - 450	4.00	#65-927	£182.98 Volume Pricing	2 In Stock
50.00	-	Fused Silica	50/50	250 - 450	4.00	#48-192	£203.99 Volume Pricing	3 In Stock
#72-251 New								
						 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
-	35.00 x 50.00	Fused Silica	50/50	250 - 450	4.00		£189.98 Volume Pricing	1 In Stock
-	50.0 x 50.0	Fused Silica	50/50	250 - 450	4.00	#48-193	£203.99 Volume Pricing	5 In Stock
10.00	-	Fused Silica	70/30	250 - 450	1.00	#84-483	£99.81 Volume Pricing	10 In Stock
12.50	-	Fused Silica	70/30	250 - 450	2.00	#84-484	£101.56 Volume Pricing	13 In Stock

-	12.5 x 12.5	Fused Silica	70/30	250 - 450	2.00	#84-485	£101.56 Volume Pricing	16 In Stock
20.00	-	Fused Silica	70/30	250 - 450	2.00	#84-486	£112.94 Volume Pricing	11 In Stock
25.00	-	Fused Silica	70/30	250 - 450	2.00	#84-487	£122.57 Volume Pricing	Contact Us
30.00	-	Fused Silica	70/30	250 - 450	3.00	#84-489	£140.96 Volume Pricing	12 In Stock
40.00	-	Fused Silica	70/30	250 - 450	4.00	#84-490	£182.98 Volume Pricing	5 In Stock
50.00	-	Fused Silica	70/30	250 - 450	4.00	#84-491	£203.99 Volume Pricing	2 In Stock
-	50.0 x 50.0	Fused Silica	70/30	250 - 450	4.00	#84-492	£203.99 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com