




[All Products](#) / [Optomechanics](#) / [Iris and Apertures](#) / [Iris Diaphragms](#)

TECHSPEC® High Performance Motorizable Irises



- Fast Accurate Repeatable Motion
- Dual Control Gear and Lever Mechanics
- Removable Pin for OEM Integration
- Anti-Reflection (AR) Leaves Available
- Iris Diaphragm Mounts and Motor Sold Separately

Technical Information



Products

Minimum Aperture (mm)	Maximum Aperture (mm)	Outer Diameter (mm)	Number of Leaves	Construction	Stock Number	Price	Buy
0.9	7.0	12.0	8	Brass-Spring Steel	#34-286	£104.18 Volume Pricing	2 In Stock
0.9	8.0	14.8	8	Brass-Spring Steel	#34-287	£63.91 Volume Pricing	20+ In Stock
1.0	12.0	19.8	10	Brass-Spring Steel	#34-288	£69.16 Volume Pricing	20+ In Stock
1.2	15.0	24.0	12	Brass-Spring Steel	#34-289	£69.16 Volume Pricing	17 In Stock
1.2	18.0	28.0	12	Brass-Spring Steel	#34-290	£69.16 Volume Pricing	20+ In Stock
1.4	22.0	33.0	14	Brass-Spring Steel	#34-291	£86.67 Volume Pricing	Contact Us
1.4	25.0	37.0	14	Brass-Spring Steel	#34-292	£86.67 Volume Pricing	20+ In Stock
1.5	28.0	40.0	16	Brass-Spring Steel	#34-293	£91.05 Volume Pricing	Contact Us
1.5	34.0	49.0	14	Brass-Spring Steel	#34-294	£104.18 Volume Pricing	20+ In Stock
0.9	7.0	12.0	8	Brass-Spring Steel, Anti-Reflection (AR) Leaves	#24-202	£146.21 Volume Pricing	20+ In Stock
1.0	12.0	19.8	10	Brass-Spring Steel, Anti-Reflection (AR) Leaves	#24-203	£98.93 Volume Pricing	20+ In Stock
1.4	22.0	33.0	14	Brass-Spring Steel, Anti-Reflection (AR) Leaves	#24-204	£121.69 Volume Pricing	20+ In Stock
1.5	28.0	40.0	16	Aluminum-Spring Steel, Anti-Reflection (AR) Leaves	#24-205	£129.57 Volume Pricing	20+ In Stock
1.5	34.0	49.0	14	Brass-Spring Steel, Anti-Reflection (AR) Leaves	#24-206	£146.21 Volume Pricing	9 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com