

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Convex \(DCX\) Lenses](#)

TECHSPEC® NIR I Coated Double-Convex (DCX) Lenses



- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Minimize Aberrations Including Spherical and Coma
- [UV Fused Silica DCX Lenses](#) Available
- Other Coating Options Available: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [NIR II](#), [VIS-EXT](#), [VIS-NIR](#), and [YAG-BBAR](#)

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed



Optical Properties

Coating: NIR I (600-1050nm)

Coating Specification:	$R_{\text{avg}} \leq 0.5\% @ 600 - 1050\text{nm}$	Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	$\lambda/4$	Focal Length Specification Wavelength (nm):	587.6
Wavelength Range (nm):	600 - 1050	Damage Threshold, By Design:	$7 \text{ J/cm}^2 @ 1064\text{nm}, 10\text{ns}$

Technical Information

NIR I Coating
 $R_{avg} \leq 0.5\%$ @ 600 - 1050nm
Typ. Energy Density Limit: 7 J/cm² @ 1064nm, 10ns



Products

Dia. (mm)	BFL (mm)	EFL (mm)	Coating	Substrate	Stock Number	Price	Buy
3.00	2.21	3.00	NIR I (600-1050nm)	N-SF5	#49-451	£56.46 Volume Pricing	12 In Stock
3.00	3.78	4.50	NIR I (600-1050nm)	N-BK7	#49-452	£56.46 Volume Pricing	Contact Us
3.00	5.37	6.00	NIR I (600-1050nm)	N-BK7	#49-453	£56.46 Volume Pricing	5 In Stock
3.00	8.46	9.00	NIR I (600-1050nm)	N-BK7	#49-454	£56.46 Volume Pricing	20+ In Stock
4.50	3.70	4.50	NIR I (600-1050nm)	N-LASF44	#49-455	£56.46 Volume Pricing	5 In Stock
4.50	8.16	9.00	NIR I (600-1050nm)	N-BK7	#49-456	£56.46 Volume Pricing	8 In Stock
5.00	4.19	5.00	NIR I (600-1050nm)	N-SF5	#63-626	£45.08 Volume Pricing	15 In Stock
5.00	9.31	10.00	NIR I (600-1050nm)	N-BK7	#63-627	£45.08 Volume Pricing	9 In Stock
5.00	14.33	15.00	NIR I (600-1050nm)	N-BK7	#63-628	£45.08 Volume Pricing	14 In Stock
5.00	19.50	20.00	NIR I (600-1050nm)	N-BK7	#63-629	£45.08 Volume Pricing	Contact Us
5.00	24.50	25.00	NIR I (600-1050nm)	N-BK7	#63-630	£45.08 Volume Pricing	Contact Us
6.00	5.19	6.00	NIR I (600-1050nm)	N-SF5	#49-457	£35.90 Volume Pricing	15 In Stock
6.00	8.22	9.00	NIR I (600-1050nm)	N-BK7	#49-458	£35.90 Volume Pricing	8 In Stock
6.00	11.18	12.00	NIR I (600-1050nm)	N-BK7	#49-459	£35.90 Volume Pricing	20+ In Stock
6.00	17.26	18.00	NIR I (600-1050nm)	N-BK7	#49-460	£35.90 Volume Pricing	14 In Stock
6.00	23.13	24.00	NIR I (600-1050nm)	N-BK7	#49-461	£35.90 Volume Pricing	Contact Us

6.00	29.23	30.00	NIR I (600-1050nm)	N-BK7	#49-462	£35.90 Volume Pricing	7 In Stock
6.00	35.33	36.00	NIR I (600-1050nm)	N-BK7	#49-463	£35.90 Volume Pricing	4 In Stock
9.00	7.90	9.00	NIR I (600-1050nm)	N-SF5	#49-464	£36.77 Volume Pricing	7 In Stock
9.00	12.56	13.50	NIR I (600-1050nm)	N-BK7	#49-465	£36.77 Volume Pricing	20+ In Stock
9.00	17.12	18.00	NIR I (600-1050nm)	N-BK7	#49-466	£36.77 Volume Pricing	1 In Stock
9.00	26.08	27.00	NIR I (600-1050nm)	N-BK7	#49-467	£36.77 Volume Pricing	6 In Stock
9.00	35.15	36.00	NIR I (600-1050nm)	N-BK7	#49-468	£36.77 Volume Pricing	Contact Us
9.00	44.17	45.00	NIR I (600-1050nm)	N-BK7	#49-469	£36.77 Volume Pricing	20+ In Stock
10.00	8.89	10.00	NIR I (600-1050nm)	N-SF5	#63-631	£36.77 Volume Pricing	20+ In Stock
10.00	13.80	15.00	NIR I (600-1050nm)	N-BK7	#63-632	£36.77 Volume Pricing	13 In Stock
10.00	19.16	20.00	NIR I (600-1050nm)	N-BK7	#63-633	£36.77 Volume Pricing	Contact Us
10.00	24.16	25.00	NIR I (600-1050nm)	N-BK7	#63-634	£36.77 Volume Pricing	1 In Stock
10.00	29.17	30.00	NIR I (600-1050nm)	N-BK7	#63-635	£36.77 Volume Pricing	5 In Stock
10.00	39.16	40.00	NIR I (600-1050nm)	N-BK7	#63-636	£36.77 Volume Pricing	11 In Stock
10.00	49.17	50.00	NIR I (600-1050nm)	N-BK7	#63-637	£36.77 Volume Pricing	3 In Stock
10.00	99.17	100.00	NIR I (600-1050nm)	N-BK7	#63-638	£36.77 Volume Pricing	20+ In Stock
12.00	10.79	12.00	NIR I (600-1050nm)	N-SF5	#49-474	£39.40 Volume Pricing	5 In Stock
12.00	16.81	18.00	NIR I (600-1050nm)	N-BK7	#49-475	£38.52 Volume Pricing	20+ In Stock
12.00	22.65	24.00	NIR I (600-1050nm)	N-BK7	#33-392	£38.52 Volume Pricing	10 In Stock

12.00	28.75	30.00	NIR I (600-1050nm)	N-BK7	#49-477	£38.52 Volume Pricing	20+ In Stock
12.00	34.90	36.00	NIR I (600-1050nm)	N-BK7	#49-478	£38.52 Volume Pricing	9 In Stock
12.00	47.09	48.00	NIR I (600-1050nm)	N-BK7	#49-479	£38.52 Volume Pricing	5 In Stock
12.00	71.07	72.00	NIR I (600-1050nm)	N-BK7	#49-480	£38.52 Volume Pricing	5 In Stock
15.00	13.68	15.00	NIR I (600-1050nm)	N-SF11	#49-481	£39.40 Volume Pricing	15 In Stock
15.00	18.99	20.00	NIR I (600-1050nm)	N-SF11	#63-639	£38.52 Volume Pricing	20+ In Stock
15.00	21.29	22.50	NIR I (600-1050nm)	N-SF11	#49-482	£38.52 Volume Pricing	Contact Us
15.00	23.82	25.00	NIR I (600-1050nm)	N-BK7	#63-640	£38.52 Volume Pricing	Contact Us
15.00	28.82	30.00	NIR I (600-1050nm)	N-BK7	#49-483	£38.52 Volume Pricing	14 In Stock
15.00	44.00	45.00	NIR I (600-1050nm)	N-BK7	#63-641	£38.52 Volume Pricing	3 In Stock
15.00	49.00	50.00	NIR I (600-1050nm)	N-BK7	#49-484	£38.52 Volume Pricing	8 In Stock
15.00	59.00	60.00	NIR I (600-1050nm)	N-BK7	#63-642	£38.52 Volume Pricing	20+ In Stock
18.00	16.69	18.00	NIR I (600-1050nm)	N-SF11	#63-643	£39.40 Volume Pricing	5 In Stock
18.00	25.25	27.00	NIR I (600-1050nm)	N-BK7	#49-485	£39.40 Volume Pricing	20+ In Stock
18.00	34.59	36.00	NIR I (600-1050nm)	N-BK7	#49-486	£39.40 Volume Pricing	17 In Stock
20.00	18.55	20.00	NIR I (600-1050nm)	N-SF11	#63-646	£40.06 Volume Pricing	6 In Stock
20.00	23.86	25.00	NIR I (600-1050nm)	N-SF11	#63-647	£40.06 Volume Pricing	Contact Us
20.00	28.20	30.00	NIR I (600-1050nm)	N-BK7	#49-487	£40.06 Volume Pricing	9 In Stock
20.00	38.44	40.00	NIR I (600-1050nm)	N-BK7	#49-488	£40.06 Volume Pricing	5 In Stock

20.00	48.84	50.00	NIR I (600-1050nm)	N-BK7	#63-648	£40.06 Volume Pricing	5 In Stock
20.00	58.67	60.00	NIR I (600-1050nm)	N-BK7	#63-649	£40.06 Volume Pricing	2 In Stock
20.00	78.67	80.00	NIR I (600-1050nm)	N-BK7	#63-650	£40.06 Volume Pricing	6 In Stock
25.00	22.47	25.00	NIR I (600-1050nm)	N-SF5	#49-489	£40.49 Volume Pricing	9 In Stock
25.00	28.31	30.00	NIR I (600-1050nm)	N-SF5	#63-651	£39.83 Volume Pricing	5 In Stock
25.00	32.81	35.00	NIR I (600-1050nm)	N-BK7	#49-490	£40.06 Volume Pricing	8 In Stock
25.00	38.21	40.00	NIR I (600-1050nm)	N-BK7	#49-491	£40.06 Volume Pricing	14 In Stock
25.00	48.29	50.00	NIR I (600-1050nm)	N-BK7	#49-492	£40.06 Volume Pricing	Contact Us
25.00	73.84	75.00	NIR I (600-1050nm)	N-BK7	#49-493	£40.06 Volume Pricing	6 In Stock
25.00	98.95	100.00	NIR I (600-1050nm)	N-BK7	#49-494	£40.06 Volume Pricing	1 In Stock
25.00	123.84	125.00	NIR I (600-1050nm)	N-BK7	#49-495	£40.06 Volume Pricing	5 In Stock
25.00	148.88	150.00	NIR I (600-1050nm)	N-BK7	#49-496	£40.06 Volume Pricing	20+ In Stock
25.00	173.94	175.00	NIR I (600-1050nm)	N-BK7	#49-497	£40.06 Volume Pricing	16 In Stock
25.00	198.35	200.00	NIR I (600-1050nm)	N-BK7	#33-398	£40.06 Volume Pricing	5 In Stock
30.00	28.12	30.00	NIR I (600-1050nm)	N-SF11	#63-652	£51.22 Volume Pricing	Contact Us
30.00	47.82	50.00	NIR I (600-1050nm)	N-BK7	#49-500	£50.35 Volume Pricing	2 In Stock
30.00	58.33	60.00	NIR I (600-1050nm)	N-BK7	#63-653	£50.35 Volume Pricing	3 In Stock
30.00	73.35	75.00	NIR I (600-1050nm)	N-BK7	#49-501	£50.35 Volume Pricing	2 In Stock
30.00	98.34	100.00	NIR I (600-1050nm)	N-BK7	#63-654	£50.35 Volume Pricing	5 In Stock

30.00	118.34	120.00	NIR I (600-1050nm)	N-BK7	#63-655	£50.35 Volume Pricing	6 In Stock
40.00	37.54	40.00	NIR I (600-1050nm)	N-SF11	#63-656	£56.46 Volume Pricing	4 In Stock
40.00	57.10	60.00	NIR I (600-1050nm)	N-BK7	#49-503	£56.46 Volume Pricing	3 In Stock
40.00	77.32	80.00	NIR I (600-1050nm)	N-BK7	#33-423	£56.46 Volume Pricing	1 In Stock
40.00	97.33	100.00	NIR I (600-1050nm)	N-BK7	#33-410	£56.46 Volume Pricing	4 In Stock
40.00	117.67	120.00	NIR I (600-1050nm)	N-BK7	#63-657	£56.46 Volume Pricing	20+ In Stock
40.00	197.35	200.00	NIR I (600-1050nm)	N-BK7	#33-417	£56.46 Volume Pricing	2 In Stock
50.00	45.30	50.00	NIR I (600-1050nm)	N-SF11	#49-508	£58.66 Volume Pricing	5 In Stock
50.00	96.65	100.00	NIR I (600-1050nm)	N-BK7	#49-509	£58.66 Volume Pricing	1 In Stock
50.00	147.00	150.00	NIR I (600-1050nm)	N-BK7	#49-510	£58.66 Volume Pricing	Contact Us
50.00	198.33	200.00	NIR I (600-1050nm)	N-BK7	#49-511	£58.66 Volume Pricing	2 In Stock
50.00	248.37	250.00	NIR I (600-1050nm)	N-BK7	#49-512	£58.66 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com