


[All Products](#) / [Test Targets](#) / [Distortion Test Targets](#)

# Diffuse Reflectance Grid Distortion Targets



- Diffuse Reflectance Treatment Mimics Ceramic Targets
- Chrome Pattern on Substrate
- No Glare with On or Off Axis Lighting
- Perfect for Front Illuminated Measuring

## Common Specifications

### General

|                     |    |
|---------------------|----|
| NIST Certification: | No |
|---------------------|----|

### Physical & Mechanical Properties

|                 |           |
|-----------------|-----------|
| Thickness (mm): | 2.00 ±0.2 |
|-----------------|-----------|

|                                                |     |
|------------------------------------------------|-----|
| Center to Center<br>Spacing Tolerance<br>(μm): | ± 1 |
|------------------------------------------------|-----|

|                                 |    |
|---------------------------------|----|
| Dot Diameter Tolerance<br>(μm): | ±3 |
|---------------------------------|----|

### Optical Properties

|          |                       |
|----------|-----------------------|
| Coating: | Low Reflective Chrome |
|----------|-----------------------|

|            |             |
|------------|-------------|
| Substrate: | Float Glass |
|------------|-------------|

## Technical Information

## Products

| Title                                                    | Stock Number            | Price                                     | Buy          |
|----------------------------------------------------------|-------------------------|-------------------------------------------|--------------|
| 2" x 2" 0.0625mm Dot, Low Reflect Grid Distortion Target | <a href="#">#62-949</a> | £632.00<br><a href="#">Volume Pricing</a> | 7 In Stock   |
| 2" x 2" 0.125mm Dot, Low Reflect Grid Distortion Target  | <a href="#">#62-950</a> | £608.00<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 2" x 2" 0.25mm Dot, Low Reflect Grid Distortion Target   | <a href="#">#62-951</a> | £592.00<br><a href="#">Volume Pricing</a> | Contact Us   |
| 3" x 3" 0.125mm Dot, Low Reflect Grid Distortion Target  | <a href="#">#62-952</a> | £760.00<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 3" x 3" 0.25mm Dot, Low Reflect Grid Distortion Target   | <a href="#">#62-953</a> | £724.00<br><a href="#">Volume Pricing</a> | Contact Us   |
| 3" x 3" 0.5mm Dot, Low Reflect Grid Distortion Target    | <a href="#">#62-954</a> | £696.00<br><a href="#">Volume Pricing</a> | 20+ In Stock |



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)