

[All Products](#) / [Optomechanics](#) / [Manual Translation Stages and Slides](#) / [Manual Stages and Slides](#)

TECHSPEC®

Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



- Four Sizes Ranging from 30 x 30mm to 125 x 125mm
- English and Metric Hole Patterns Available
- Micrometer and Lead Screw Drive Options
- Easily Configured into X-Y and X-Y-Z Configurations

Common Specifications


Physical & Mechanical Properties

Type of Movement:	Linear (X)	Guide System:	Crossed Roller Bearing
Construction:	Aluminium Stage	Straight Line Accuracy (µm):	2


Technical Information

[illegible]

30mm Standard-Top Stages - Center Drive




Top View




Bottom Plate Portion

30mm Standard-Top Stages - Side Drive




Top View




Bottom Plate Portion

40mm Standard-Top Stages - Center Drive




Top View




Bottom Plate Portion

40mm Standard-Top Stages - Side Drive




Top View




Bottom Plate Portion

70mm Standard-Top Stages - Center Drive




Top View




Bottom Plate Portion

70mm Standard-Top Stages - Side Drive




Top View




Bottom Plate Portion

125mm Standard-Top Stages - Center Drive





Top View



Bottom Plate Portion

125mm Standard-Top Stages - Side Drive



Products

Stage Size (mm)	Type	Type of Drive	Drive Orientation	Travel (mm)	Travel (inches)	Stock Number	Price	Buy
30 x 30	English	Lead Screw	Center Drive	-	0.5	#66-386	£285.41 Volume Pricing	Contact Us
30 x 30	English	English Micrometer	Center Drive	-	0.5	#66-387	£348.45 Volume Pricing	2 In Stock
30 x 30	English	Lead Screw	Side Drive	-	0.5	#66-388	£285.41 Volume Pricing	2 In Stock
30 x 30	English	English Micrometer	Side Drive	-	0.5	#66-389	£348.45 Volume Pricing	4 In Stock
30 x 30	Metric	Lead Screw	Center Drive	13	-	#66-390	£285.41 Volume Pricing	6 In Stock
30 x 30	Metric	Metric Micrometer	Center Drive	13	-	#66-391	£348.45 Volume Pricing	20+ In Stock
30 x 30	Metric	Lead Screw	Side Drive	13	-	#66-392	£285.41 Volume Pricing	Contact Us
30 x 30	Metric	Metric Micrometer	Side Drive	13	-	#66-393	£348.45 Volume Pricing	20+ In Stock
40 x 40	English	Lead Screw	Center Drive	-	0.5	#66-402	£310.80 Volume Pricing	1 In Stock
40 x 40	English	English Micrometer	Center Drive	-	0.5	#66-403	£344.95 Volume Pricing	3 In Stock
40 x 40	English	English Micrometer	Center Drive	-	1	#66-404	£365.96 Volume Pricing	5 In Stock
40 x 40	English	Lead Screw	Side Drive	-	0.5	#66-405	£310.80 Volume Pricing	3 In Stock
40 x 40	English	English Micrometer	Side Drive	-	0.5	#66-406	£344.95 Volume Pricing	4 In Stock
40 x 40	English	English Micrometer	Side Drive	-	1	#66-407	£365.96 Volume Pricing	2 In Stock
40 x 40	Metric	Lead Screw	Center Drive	13	-	#66-408	£310.80 Volume Pricing	20+ In Stock
40 x 40	Metric	Metric Micrometer	Center Drive	13	-	#66-409	£344.95 Volume Pricing	14 In Stock
40 x 40	Metric	Metric Micrometer	Center Drive	25	-	#66-410	£365.96 Volume Pricing	13 In Stock

40 x 40	Metric	Lead Screw	Side Drive	13	-	#66-411	£310.80 Volume Pricing	14 In Stock
40 x 40	Metric	Metric Micrometer	Side Drive	13	-	#66-412	£344.95 Volume Pricing	Contact Us
40 x 40	Metric	Metric Micrometer	Side Drive	25	-	#66-413	£365.96 Volume Pricing	4 In Stock
70 x 70	English	English Micrometer	Center Drive	-	1	#66-428	£468.39 Volume Pricing	6 In Stock
70 x 70	English	Lead Screw	Side Drive	-	0.5	#66-429	£384.34 Volume Pricing	3 In Stock
70 x 70	English	English Micrometer	Side Drive	-	0.5	#66-430	£419.36 Volume Pricing	5 In Stock
70 x 70	English	English Micrometer	Side Drive	-	1	#66-431	£468.39 Volume Pricing	5 In Stock
70 x 70	Metric	Lead Screw	Center Drive	13	-	#66-432	£384.34 Volume Pricing	5 In Stock
70 x 70	Metric	Metric Micrometer	Center Drive	13	-	#66-433	£419.36 Volume Pricing	Contact Us
70 x 70	Metric	Metric Micrometer	Center Drive	25	-	#66-434	£468.39 Volume Pricing	2 In Stock
70 x 70	Metric	Lead Screw	Side Drive	13	-	#66-435	£384.34 Volume Pricing	3 In Stock
70 x 70	Metric	Metric Micrometer	Side Drive	13	-	#66-436	£419.36 Volume Pricing	3 In Stock
70 x 70	Metric	Metric Micrometer	Side Drive	25	-	#66-437	£468.39 Volume Pricing	Contact Us
70 x 70	English	Lead Screw	Center Drive	-	0.5	#66-426	£384.34 Volume Pricing	1 In Stock
70 x 70	English	English Micrometer	Center Drive	-	0.5	#66-427	£419.36 Volume Pricing	5 In Stock
125 x 125	English	Lead Screw	Center Drive	-	1	#66-450	£529.68 Volume Pricing	1 In Stock
125 x 125	English	English Micrometer	Center Drive	-	1	#66-451	£560.32 Volume Pricing	1 In Stock
125 x 125	English	English Micrometer	Center Drive	-	2	#66-452	£674.14 Volume Pricing	3 In Stock
125 x 125	English	Lead Screw	Side Drive	-	1	#66-453	£529.68 Volume Pricing	1 In Stock
125 x 125	English	English Micrometer	Side Drive	-	1	#66-454	£560.32 Volume Pricing	5 In Stock

125 x 125	English	English Micrometer	Side Drive	-	2	#66-455	£674.14 Volume Pricing	4 In Stock
125 x 125	Metric	Lead Screw	Center Drive	25	-	#66-456	£529.68 Volume Pricing	2 In Stock
125 x 125	Metric	Metric Micrometer	Center Drive	25	-	#66-457	£560.32 Volume Pricing	6 In Stock
125 x 125	Metric	Metric Micrometer	Center Drive	50	-	#66-458	£674.14 Volume Pricing	1 In Stock
125 x 125	Metric	Lead Screw	Side Drive	25	-	#66-459	£529.68 Volume Pricing	2 In Stock
125 x 125	Metric	Metric Micrometer	Side Drive	25	-	#66-460	£560.32 Volume Pricing	1 In Stock
125 x 125	Metric	Metric Micrometer	Side Drive	50	-	#66-461	£674.14 Volume Pricing	1 In Stock
30 x 30	English	English Micrometer	Center Drive	-	0.25	#83-503	£348.45 Volume Pricing	20+ In Stock
30 x 30	English	English Micrometer	Side Drive	-	0.25	#83-504	£348.45 Volume Pricing	5 In Stock
30 x 30	Metric	Metric Micrometer	Center Drive	6.5	-	#83-505	£348.45 Volume Pricing	11 In Stock
30 x 30	Metric	Metric Micrometer	Side Drive	6.5	-	#83-506	£348.45 Volume Pricing	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com