

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® C Series Fixed Focal Length VIS-NIR Lenses



- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) Broadband Lens for 425-1000nm Wavelength Range
- 3.5mm to 50mm Focal Length

Common Specifications

General

Imaging Lens Type:

Compact Lens Coated for Visible to Near Infrared

Physical & Mechanical Properties

Iris Option:

Variable

Optical Properties

Coating:

425 - 1000nm BBAR

Coating Specification:

425 - 1000nm BBAR

Threading & Mounting

Mount:

C-Mount

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
3.50	1/1.8"	f/2 - f/11	0 - ∞	C-Mount	#39-937	£502.00	7 In Stock
4.50	1/1.8"	f/2 - f/11	25 - ∞	C-Mount	#39-938	£502.00	Contact Us
6.00	1/1.8"	f/1.4 - f/16	75 - ∞	C-Mount	#39-939	£427.00	6 In Stock
8.50	2/3"	f/1.3 - f/16	100 - ∞	C-Mount	#27-553	£467.50	20+ In Stock
12.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#27-554	£467.50	10 In Stock
16.00	2/3"	f/1.6 - f/16	100 - ∞	C-Mount	#67-714	£372.00	20+ In Stock
25.00	2/3"	f/1.4 - f/16	100 - ∞	C-Mount	#67-715	£372.00	Contact Us
35.00	2/3"	f/1.65 - f/22	165 - ∞	C-Mount	#67-716	£372.00	20+ In Stock
50.00	2/3"	f/2 - f/22	250 - ∞	C-Mount	#67-717	£412.00	6 In Stock
#74-054 New							
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
75.00	2/3"	f/2.0 - f/16.0	500 - ∞	C-Mount		£510.00	Contact Us
100.00	4/3"	f/2.8 - f/22	750 - ∞	C-Mount	#27-555	£561.00	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com