

[All Products](#) / [Lab and Production](#) / [Optical Adhesives](#)

Preloaded Norland Optical Adhesive Syringes See More by [Norland](#)



- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Technical Information

Products

Norland Number	Size (oz)	Bonding Type	Glass Bonding	Metal Bonding	Index of Refraction (n _d)	Stock Number	Price	Buy
60	0.1	Glass to Glass	Good	Good	1.56	#55-154	£22.00 Volume Pricing	3 In Stock
60	0.34	Glass to Glass	Good	Good	1.56	#55-084	£27.20 Volume Pricing	4 In Stock
61	0.1	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-155	£22.00 Volume Pricing	20+ In Stock
61	0.34	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-085	£27.20 Volume Pricing	20+ In Stock
63	0.1	Glass to Glass	Good	Good	1.56	#55-156	£22.00 Volume Pricing	4 In Stock
63	0.34	Glass to Glass	Good	Good	1.56	#55-086	£27.20 Volume Pricing	2 In Stock
65	0.1	Glass to Glass/Metal	Good	Good	1.52	#55-157	£22.00 Volume Pricing	5 In Stock
65	0.34	Glass to Glass/Metal	Good	Good	1.52	#55-087	£27.20 Volume Pricing	Contact Us
68	0.1	Plastic to Plastic/Glass	Excellent	Good	1.54	#55-158	£22.00 Volume Pricing	Contact Us
68	0.34	Plastic to Plastic/Glass	Excellent	Good	1.54	#55-088	£27.20 Volume Pricing	7 In Stock
68T	0.1	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-390	£22.00 Volume Pricing	1 In Stock
68T	0.34	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-391	£27.20 Volume Pricing	2 In Stock
68TH	0.1	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-789	£22.00 Volume Pricing	5 In Stock
68TH	0.34	Plastic to Plastic/Glass	Excellent	Good	1.54	#14-790	£31.60 Volume Pricing	4 In Stock
72	0.1	Plastic to Plastic/Glass	Excellent	Good	1.56	#17-386	£22.00 Volume Pricing	2 In Stock
72	0.34	Plastic to Plastic/Glass	Excellent	Good	1.56	#17-365	£31.60 Volume Pricing	Contact Us
73	0.1	Glass to Glass	Excellent	Good	1.56	#17-387	£22.00 Volume Pricing	1 In Stock

73	0.34	Glass to Glass	Excellent	Good	1.56	#17-366	£31.60 Volume Pricing	1 In Stock
74	0.1	Plastic to Plastic/Glass	Excellent	Good	1.52	#17-388	£22.00 Volume Pricing	2 In Stock
74	0.34	Plastic to Plastic/Glass	Excellent	Good	1.52	#17-367	£31.60 Volume Pricing	4 In Stock
76	0.1	Glass to Plastic	Excellent	Good	1.51	#17-389	£22.00 Volume Pricing	2 In Stock
76	0.34	Glass to Plastic	Excellent	Good	1.51	#17-368	£31.60 Volume Pricing	3 In Stock
78	0.1	Plastic to Plastic/Glass	Excellent	Good	1.50	#17-390	£22.00 Volume Pricing	2 In Stock
78	0.34	Plastic to Plastic/Glass	Excellent	Good	1.50	#17-369	£31.60 Volume Pricing	1 In Stock
81	0.1	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-159	£22.00 Volume Pricing	3 In Stock
81	0.34	Glass to Glass/Metal	Excellent	Excellent	1.56	#55-089	£27.20 Volume Pricing	3 In Stock
86H	0.1	Glass to Glass/Plastic	Excellent	Good	1.55	#12-846	£22.00 Volume Pricing	Contact Us
86H	0.34	Glass to Glass/Plastic	Excellent	Good	1.55	#12-847	£27.20 Volume Pricing	Contact Us
86TH	0.1	Glass to Glass/Plastic	Excellent	Good	1.54	#17-391	£22.00 Volume Pricing	Contact Us
86TH	0.34	Glass to Glass/Plastic	Excellent	Good	1.54	#17-370	£31.60 Volume Pricing	Contact Us
86TLH	0.1	Glass to Glass/Metal	Excellent	Excellent	1.55	#14-795	£22.00 Volume Pricing	Contact Us
86TLH	0.34	Glass to Glass/Metal	Excellent	Excellent	1.55	#14-796	£31.60 Volume Pricing	Contact Us
87	0.1	Glass to Glass/Plastic	Excellent	Good	1.52	#17-392	£22.00 Volume Pricing	3 In Stock
87	0.34	Glass to Glass/Plastic	Excellent	Good	1.52	#17-371	£31.60 Volume Pricing	2 In Stock
88	0.1	Glass to Glass/Metal	Excellent	Excellent	1.56	#14-839	£22.00 Volume Pricing	5 In Stock
88	0.34	Glass to Glass/Metal	Excellent	Excellent	1.56	#14-840	£31.60 Volume Pricing	3 In Stock
89H	0.1	Glass to Glass	Excellent	Good	1.51	#17-393	£22.00 Volume Pricing	2 In Stock

89H	0.34	Glass to Glass	Excellent	Good	1.51	#17-372	£31.60 Volume Pricing	3 In Stock
UVS 91	0.1	Liquid Crystal Displays	Excellent	Good	N/A	#17-406	£22.00 Volume Pricing	5 In Stock
UVS 91	0.34	Liquid Crystal Displays	Excellent	Good	N/A	#17-385	£31.60 Volume Pricing	2 In Stock
108H	0.1	Glass to Metal	Excellent	Excellent	1.51	#17-405	£22.00 Volume Pricing	2 In Stock
108H	0.34	Glass to Metal	Excellent	Excellent	1.51	#17-384	£31.60 Volume Pricing	2 In Stock
139	0.1	Glass to Glass	Excellent	Good	1.39	#15-694	£31.60 Volume Pricing	1 In Stock
139	0.34	Glass to Glass	Excellent	Good	1.39	#15-695	£91.20 Volume Pricing	2 In Stock
144	0.1	Glass to Glass	Excellent	Good	1.44	#17-400	£22.00 Volume Pricing	2 In Stock
144	0.34	Glass to Glass	Excellent	Good	1.44	#17-379	£46.00 Volume Pricing	1 In Stock
146H	0.1	Plastic to Plastic/Glass	Excellent	Good	1.46	#12-864	£22.00 Volume Pricing	1 In Stock
146H	0.34	Plastic to Plastic/Glass	Excellent	Good	1.46	#12-865	£27.20 Volume Pricing	1 In Stock
148	0.1	Glass to Glass	Excellent	Good	1.48	#17-401	£22.00 Volume Pricing	1 In Stock
148	0.34	Glass to Glass	Excellent	Good	1.48	#17-380	£31.60 Volume Pricing	3 In Stock
160	0.1	Glass to Glass	Excellent	Good	1.60	#12-858	£22.00 Volume Pricing	Contact Us
160	0.34	Glass to Glass	Excellent	Good	1.60	#12-859	£27.20 Volume Pricing	2 In Stock
165H	0.1	Glass to Glass	Excellent	Excellent	1.65	#17-404	£22.00 Volume Pricing	2 In Stock
165H	0.34	Glass to Glass	Excellent	Excellent	1.65	#17-383	£31.60 Volume Pricing	2 In Stock
170	0.1	Glass to Glass	Excellent	Good	1.70	#12-849	£33.60 Volume Pricing	3 In Stock
170	0.34	Glass to Glass	Excellent	Good	1.70	#12-850	£81.60 Volume Pricing	4 In Stock
170F	0.1	Glass to Glass	Excellent	Good	1.70	#14-792	£36.80 Volume Pricing	2 In Stock

170F	0.34	Glass to Glass	Excellent	Good	1.70	#14-793	£86.40 Volume Pricing	2 In Stock
1348	0.1	Glass to Glass	Good	Good	1.348	#12-855	£31.60 Volume Pricing	Contact Us
1348	0.34	Glass to Glass	Good	Good	1.348	#12-856	£91.20 Volume Pricing	1 In Stock
1369	0.1	Glass to Glass	Good	Good	1.369	#17-394	£41.20 Volume Pricing	1 In Stock
1369	0.34	Glass to Glass	Good	Good	1.369	#17-373	£98.40 Volume Pricing	2 In Stock
1375	0.1	Glass to Glass	Excellent	Good	1.375	#17-395	£22.00 Volume Pricing	Contact Us
1375	0.34	Glass to Glass	Excellent	Good	1.375	#17-374	£46.00 Volume Pricing	1 In Stock
1422	0.1	Glass to Glass	Excellent	Good	1.422	#17-399	£41.20 Volume Pricing	2 In Stock
1422	0.34	Glass to Glass	Excellent	Good	1.422	#17-378	£98.40 Volume Pricing	2 In Stock
1622H	0.1	Glass to Glass	Excellent	Excellent	1.622	#17-402	£22.00 Volume Pricing	Contact Us
1622H	0.34	Glass to Glass	Excellent	Excellent	1.622	#17-381	£46.00 Volume Pricing	Contact Us
1639H	0.1	Glass to Glass	Excellent	Excellent	1.639	#17-403	£22.00 Volume Pricing	Contact Us
1639H	0.34	Glass to Glass	Excellent	Excellent	1.639	#17-382	£46.00 Volume Pricing	Contact Us
1665	0.1	Glass to Glass	Excellent	Good	1.665	#12-861	£22.00 Volume Pricing	2 In Stock
1665	0.34	Glass to Glass	Excellent	Good	1.665	#12-862	£46.00 Volume Pricing	1 In Stock
13685	0.1	Glass to Glass	Excellent	Good	1.3685	#12-852	£22.00 Volume Pricing	2 In Stock
13685	0.34	Glass to Glass	Excellent	Good	1.3685	#12-853	£46.00 Volume Pricing	2 In Stock
13775	0.1	Glass to Glass	Good	Good	1.3775	#17-396	£41.20 Volume Pricing	1 In Stock
13775	0.34	Glass to Glass	Good	Good	1.3775	#17-375	£98.40 Volume Pricing	1 In Stock
13825	0.1	Glass to Glass	Good	Good	1.3825	#17-397	£41.20 Volume Pricing	4 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com