

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

Astronomy Bandpass Filters



- Filter and Measure Light from Astronomical Objects
- Ideal for Photometric Calibration
- UBVRI Filters

Common Specifications

Physical & Mechanical Properties

Thickness (mm): 5.00 ±0.1



Parallelism (arcsec): <30

Optical Properties

Surface Quality: 60-40

Transmitted Wavefront, RMS: $\lambda/4$

Technical Information



Products

Dia. (mm)	Dimensions (mm)	CWL (nm)	FWHM (nm)	Type of Filter	Stock Number	Price	Buy
25.00	-	365.00	60.00	Kron- Cousins, U	#21-103	£252.14 Volume Pricing	1 In Stock
25.00	-	440.00	100.00	Kron- Cousins, B	#21-104	£252.14 Volume Pricing	1 In Stock
25.00	-	520.00	90.00	Kron- Cousins, V	#21-105	£252.14 Volume Pricing	1 In Stock
25.00	-	630.00	250.00	Kron- Cousins, R	#21-106	£252.14 Volume Pricing	3 In Stock
25.00	-	900.00	175.00	Kron- Cousins, I	#21-107	£252.14 Volume Pricing	1 In Stock
50.00	-	365.00	60.00	Kron- Cousins, U	#21-109	£726.67 Volume Pricing	1 In Stock
50.00	-	440.00	100.00	Kron- Cousins, B	#21-110	£726.67 Volume Pricing	1 In Stock
50.00	-	520.00	90.00	Kron- Cousins, V	#21-111	£726.67 Volume Pricing	1 In Stock
50.00	-	630.00	250.00	Kron- Cousins, R	#21-112	£726.67 Volume Pricing	Contact Us
50.00	-	900.00	175.00	Kron- Cousins, I	#21-113	£726.67 Volume Pricing	Contact Us
-	50 x 50	365.00	60.00	Kron- Cousins, U	#21-115	£726.67 Volume Pricing	1 In Stock
-	50 x 50	440.00	100.00	Kron- Cousins, B	#21-116	£726.67 Volume Pricing	1 In Stock
-	50 x 50	520.00	90.00	Kron- Cousins, V	#21-117	£726.67 Volume Pricing	1 In Stock

-	50 x 50	630.00	250.00	Kron-Cousins, R	#21-118	£726.67 Volume Pricing	Contact Us
-	50 x 50	900.00	175.00	Kron-Cousins, I	#21-119	£726.67 Volume Pricing	1 In Stock
25.00	-	365.00	60.00	Johnson-Bessel, U	#21-121	£252.14 Volume Pricing	1 In Stock
25.00	-	440.00	100.00	Johnson-Bessel, B	#21-122	£252.14 Volume Pricing	1 In Stock
25.00	-	520.00	90.00	Johnson-Bessel, V	#21-123	£252.14 Volume Pricing	1 In Stock
25.00	-	630.00	120.00	Johnson-Bessel, R	#21-124	£252.14 Volume Pricing	1 In Stock
25.00	-	900.00	300.00	Johnson-Bessel, I	#21-125	£252.14 Volume Pricing	1 In Stock
50.00	-	365.00	60.00	Johnson-Bessel, U	#21-127	£726.67 Volume Pricing	1 In Stock
50.00	-	440.00	100.00	Johnson-Bessel, B	#21-128	£726.67 Volume Pricing	1 In Stock
50.00	-	520.00	90.00	Johnson-Bessel, V	#21-129	£726.67 Volume Pricing	1 In Stock
50.00	-	630.00	120.00	Johnson-Bessel, R	#21-130	£726.67 Volume Pricing	1 In Stock
50.00	-	900.00	300.00	Johnson-Bessel, I	#21-131	£726.67 Volume Pricing	1 In Stock
-	50 x 50	365.00	60.00	Johnson-Bessel, U	#21-133	£726.67 Volume Pricing	1 In Stock
-	50 x 50	440.00	100.00	Johnson-Bessel, B	#21-134	£726.67 Volume Pricing	1 In Stock
-	50 x 50	520.00	90.00	Johnson-Bessel, V	#21-135	£726.67 Volume Pricing	1 In Stock
-	50 x 50	630.00	120.00	Johnson-Bessel, R	#21-136	£726.67 Volume Pricing	1 In Stock
-	50 x 50	900.00	300.00	Johnson-Bessel, I	#21-137	£726.67 Volume Pricing	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com