

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [UV and IR Plano-Convex \(PCX\) Lenses](#)

# ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

See More by [ISP Optics](#)



- Low Dispersion and Absorption from 0.6 – 18μm
- High Resistance to Thermal Shock
- Uncoated or BBAR Coated for 8 – 12μm

## Common Specifications

### Physical & Mechanical Properties



<b>Bevel:</b>	Protective as needed	<b>Centering (arcmin):</b>	<3
---------------	----------------------	----------------------------	----

### Optical Properties

<b>Substrate:</b>	Zinc Selenide (ZnSe), CVD Grade	<b>Focal Length Tolerance (%):</b>	±2
<b>Surface Quality:</b>	60-40	<b>Irregularity (P-V) @ 10.6μm:</b>	λ/20

## Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Model Number	Stock Number	Price	Buy
<a href="#">#24-947 Clearance</a>							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	200.00	199.52	Uncoated	ZC-PX-25-200		£304.26	1 In Stock
<a href="#">#24-952 Clearance</a>							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
38.10	75.00	74.14	Uncoated	ZC-PX-38-76		£254.11	6 In Stock

[#24-953 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

38.10 100.00 98.41 Uncoated ZC-PX-38-100

£254.11

3 In Stock

---

[#24-956 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

38.10 200.00 199.39 Uncoated ZC-PX-38-200

£254.11

5 In Stock

---

[#24-961 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

50.80 100.00 97.78 Uncoated ZC-PX-50-100

£414.76

3 In Stock

---

[#24-982 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

12.70 25.40 24.56 BBAR (8000-12000nm) AR812-ZC-PX-12-25

£105.36

14 In Stock

---

[#24-992 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

25.40	500.00	496.87	BBAR (8000- 12000nm)	AR812- ZC-PX- 25-500	£176.76	1 In Stock
-------	--------	--------	----------------------------	----------------------------	---------	------------

---

[#24-994 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

38.10	63.50	61.84	BBAR (8000- 12000nm)	AR812- ZC-PX- 38-63	£283.86	3 In Stock
-------	-------	-------	----------------------------	---------------------------	---------	------------

[#24-999 Clearance](#)



Clearance

Availability  
is limited,  
so buy  
before  
these  
products  
disappear.  
Sorry, we  
cannot  
accept  
returns.  
Receive  
up to 80%  
off select  
products.

38.10	200.00	199.39	BBAR (8000- 12000nm)	AR812- ZC-PX- 38-200	£283.86	2 In Stock
-------	--------	--------	----------------------------	----------------------------	---------	------------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)