

[All Products](#) / [Optics](#) / [Fiber Optics](#)

Single Mode Fiber Optic Patchcords



- FC/PC, FC/APC, and Hybrid Terminated Connectors
- Patchcords for Wavelengths from 450 – 1650nm
- 1m, 2m and 5m Standardized Lengths Available

Common Specifications

Physical & Mechanical Properties

Jacket Material:

900µm Yellow Hytrel® Tubing

Optical Properties

Numerical Aperture NA:

0.13

Technical Information

Products

Wavelength Range (nm)	Mode Field Diameter (nm)	NA	Connector	Length (m)	Stock Number	Price	Buy
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	1	#25-928	£37.40 Volume Pricing	3 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	2	#25-929	£39.10 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC	5	#71-136	£41.65	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	1	#25-930	£57.80 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	2	#25-931	£62.90 Volume Pricing	2 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC	5	#71-137	£70.55	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	1	#25-932	£76.50 Volume Pricing	7 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	2	#25-933	£82.45 Volume Pricing	4 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC	5	#71-138	£91.80	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	1	#25-934	£60.35 Volume Pricing	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC	2	#25-935	£62.05 Volume Pricing	Contact Us
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC	5	#71-139	£64.60	Contact Us
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	1	#25-936	£68.00 Volume Pricing	1 In Stock

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC	2	#25-937	£73.10 Volume Pricing	6 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC	5	#71-140	£80.75	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	1	#25-938	£58.65 Volume Pricing	3 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	2	#25-939	£60.35 Volume Pricing	1 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/APC	5	#71-141	£62.90	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	1	#25-940	£95.20 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	2	#25-941	£99.45 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/APC	5	#71-142	£106.25	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	1	#25-942	£98.60 Volume Pricing	4 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	2	#25-943	£103.70 Volume Pricing	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/APC	5	#71-143	£111.35	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	1	#25-944	£79.90 Volume Pricing	1 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/APC	2	#25-945	£81.60 Volume Pricing	Contact Us
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/APC	5	#71-144	£84.15	2 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	1	#25-946	£88.40 Volume Pricing	1 In Stock

450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/APC	2	#25-947	£91.80 Volume Pricing	1 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/APC	5	#71-145	£96.90	2 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	1	#25-948	£48.45 Volume Pricing	5 In Stock
1260 - 1625	9.2 ± 0.4µm @ 1310nm 10.4 ± 0.5µm @ 1550nm	0.13	FC/PC to FC/APC	5	#71-146	£52.70	5 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	1	#25-949	£85.00 Volume Pricing	1 In Stock
980 - 1650	5.9 ± 0.3µm @ 980nm 6.2 ± 0.3µm @ 1060nm	0.13	FC/PC to FC/APC	5	#71-147	£97.75	1 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	1	#25-950	£90.10 Volume Pricing	3 In Stock
780 - 970	5.0 ± 0.5µm @ 850nm	0.13	FC/PC to FC/APC	5	#71-148	£105.40	3 In Stock
600 - 770	3.5 - 4.5µm @ 630nm	0.13	FC/PC to FC/APC	1	#25-951	£73.95 Volume Pricing	1 In Stock
633 - 780	3.6 - 5.3µm@633nm	0.13	FC/PC to FC/APC	5	#71-149	£78.20	1 In Stock
450 - 600	3.0 - 4.0µm @ 515nm	0.13	FC/PC to FC/APC	1	#25-952	£83.30 Volume Pricing	1 In Stock
488 - 633	2.8 - 4.1µm@488nm	0.13	FC/PC to FC/APC	5	#71-150	£96.05	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com