

[All Products](#) / [Lasers](#) / [Laser Safety](#) / [Laser Safety Windows](#)

Laser Safety Windows



- CE Certified Laser Radiation Protection
- Available for UV, VIS, and NIR Wavelengths
- 200mm x 100mm Size Ideal for Small Enclosures
- 304.8mm x 304.8mm Sizes Also Available

Common Specifications

General

Filter Material:	Polymer
------------------	---------

Physical & Mechanical Properties

Thickness (mm):	3.00
-----------------	------

Technical Information

Products

Filter	Optical Density OD (Average)	Visible Light Transmission VLT (%)	Color	Stock Number	Price	Buy
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Clear	#29-372	£70.55 Volume Pricing	1 In Stock
LS02	>7 @ 180 - 532nm	48 (Photopic), 9 (Scotopic)	Amber	#29-373	£70.55 Volume Pricing	Contact Us
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Blue	#29-374	£106.25 Volume Pricing	1 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Amber	#29-375	£106.25 Volume Pricing	1 In Stock
LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Aqua	#29-376	£106.25 Volume Pricing	1 In Stock

LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Green	#29-377	£106.25 Volume Pricing	1 In Stock
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Green	#29-378	£106.25 Volume Pricing	1 In Stock
LS07	>5 @ 190 - 435nm >5 @ 730 - 1085nm >7 @ 755, 1064nm	36	Green	#29-379	£106.25 Volume Pricing	1 In Stock
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Amber	#29-380	£106.25 Volume Pricing	1 In Stock

[#75-514 New](#)



New

LS22	>5 @ 1000-1150 >7 @ 1060-1100 >5 @ 10600	50	Green	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£157.25	1 In Stock
------	---	----	-------	--	---------	------------

[#75-515 New](#)



New

LS26	>5 @ 190- 533 >4 @ 850- 879 >5 @880- 1100 >6 @ 1064 >5 @ 10600	17	Amber	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£165.75	2 In Stock
------	---	----	-------	--	---------	------------

[#75-516 New](#)



New

LS25	>7 @ 190-515 >6 @ 516-525 >5 @ 526-532 >4 @ 533-535 >5 @ 10600	41	Orange	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£148.75	Contact Us
------	--	----	--------	--	---------	------------

[#75-518 New](#)



New

LS27	>5 @ 190-360 >5 @ 9000-11000	90	Clear	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	£106.25	2 In Stock
------	---------------------------------	----	-------	--	---------	------------

[#75-520 New](#)



LS23	>4 @ 190-260	78	Yellow	New	£102.00	2 In Stock
	>3 @ 260-300			Launched		
	>4 @ 300-325			on our website		
	>5 @ 325-450			before appearing		
	>5 @ 9000-11000			in our latest print catalogs.		
				Be the first to buy before anyone else!		

[#75-521 New](#)



LS24	>7 @ 200-400	50	Green	New	£148.75	1 In Stock
	>7 @ 850-1100			Launched		
	>5 @ 9000-10600			on our website		
				before appearing		
				in our latest print catalogs.		
				Be the first to buy before anyone else!		

