


[All Products](#) /
 [Optics](#) /
 [Optical Lenses](#) /
 [Cylinder Lenses](#) /
 [Specialty Lenses](#)

Precision Powell Lenses



- Generate Uniform, Flat-Top Profile Over Entire Line
- Fan Angles from 1° to 75° Available
- AR Coated for 400 - 500nm or 500 - 850nm

Common Specifications

Physical & Mechanical Properties

Dimensions (mm): 8.90 +0.00/-0.15

Height (mm): 8.90 +0.00/-2.00

Optical Properties

Index of Refraction (n_d): 1.458

Technical Information

Products

Fan Angle (°)	Coating	Substrate	Stock Number	Price	Buy
5.00	BBAR (400-500nm)	N-BK7	#70-128	£268.78 Volume Pricing	Contact Us
10.00	BBAR (400-500nm)	N-BK7	#70-129	£268.78 Volume Pricing	4 In Stock
15.00	BBAR (400-500nm)	N-BK7	#70-130	£268.78 Volume Pricing	1 In Stock
20.00	BBAR (400-500nm)	N-BK7	#70-131	£268.78 Volume Pricing	Contact Us
30.00	BBAR (400-500nm)	N-BK7	#70-132	£268.78 Volume Pricing	Contact Us
45.00	BBAR (400-500nm)	N-SF6	#70-133	£268.78 Volume Pricing	1 In Stock
60.00	BBAR (400-500nm)	N-SF6	#70-134	£268.78 Volume Pricing	1 In Stock
75.00	BBAR (400-500nm)	N-SF6	#70-135	£268.78 Volume Pricing	4 In Stock
1.00	BBAR (500-850nm)	N-BK7	#70-136	£268.78 Volume Pricing	2 In Stock
5.00	BBAR (500-850nm)	N-BK7	#70-137	£268.78 Volume Pricing	Contact Us
10.00	BBAR (500-850nm)	N-BK7	#70-138	£268.78 Volume Pricing	Contact Us
15.00	BBAR (500-850nm)	N-BK7	#70-139	£268.78 Volume Pricing	Contact Us
20.00	BBAR (500-850nm)	N-BK7	#70-140	£268.78 Volume Pricing	Contact Us
30.00	BBAR (500-850nm)	N-BK7	#70-141	£268.78 Volume Pricing	Contact Us
45.00	BBAR (500-850nm)	N-SF6	#70-142	£268.78 Volume Pricing	1 In Stock
60.00	BBAR (500-850nm)	N-SF6	#70-143	£268.78 Volume Pricing	Contact Us
75.00	BBAR (500-850nm)	N-SF6	#70-144	£268.78 Volume Pricing	3 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com