

[See all 57 Products in Family](#)

TECHSPEC®

10mm Diameter, S-Mount Thin Optic Mount



Stock **#63-943** 9 In Stock

-

1

+

£32<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £32.60 each                   |
| Qty 5-9        | £29.28 each                   |
| Qty 10-25      | £27.20 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type of Optics:

Circular

Function:

Optic Mount (Fixed)

| Physical & Mechanical Properties |                                           |
|----------------------------------|-------------------------------------------|
| 8.6                              | Extension Length (mm):                    |
| 11.6                             | Total Length (mm):                        |
| 16.0                             | Outer Diameter (mm):                      |
| 9.0                              | Clear Aperture CA (mm):                   |
| 2.5                              | Max. Thickness of Compatible Optics (mm): |
| 1.0                              | Min. Thickness of Compatible Optics (mm): |

| Threading & Mounting |                                     |
|----------------------|-------------------------------------|
| 10.0                 | Diameter of Compatible Optics (mm): |
| S-Mount              | Thread Type:                        |

| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | REACH 241:                  |


## Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32 TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

**Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

## Technical Information







**S-Thread Simple / Thin Lens Mount**




**S-Thread Simple /Thin Lens Mount**



**S-Thread Achromat / Thick Lens Mount**





#58-741

