

[See all 18 Products in Family](#)

TECHSPEC®

12.7mm Thick Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock **#38-757** 1 In Stock

-

1

+

£32<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £32.80 each                   |
| Qty 5+         | £31.20 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

|                     |           |
|---------------------|-----------|
| Fixed               | Type:     |
| Optic Mount (Fixed) | Function: |

Physical & Mechanical Properties

|                                         |               |
|-----------------------------------------|---------------|
| Matte Black Anodized Aluminum (6061-T6) | Construction: |
|-----------------------------------------|---------------|

|      |                                           |
|------|-------------------------------------------|
| 14.0 | Total Length (mm):                        |
| 11.2 | Clear Aperture CA (mm):                   |
| 9.0  | Max. Thickness of Compatible Optics (mm): |
| 1.0  | Min. Thickness of Compatible Optics (mm): |
| 9.0  | Edge Thickness of Compatible Optics (mm): |

Threading & Mounting

|            |                                     |
|------------|-------------------------------------|
| 12.7       | Diameter of Compatible Optics (mm): |
| M29 x 0.75 | Thread Type:                        |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 250:                  |

## Product Details

- Mounts for a Variety of Optical Component Diameters and Thicknesses
- M29 Outer Diameter Threads Allow Easy Positioning Within [Outer Tubes](#)
- One Retainer Ring and One Delrin Ring are Included
- Click [Here](#) to See How to Use the Multi-Element Tube System Components to Build an Optical System.

TECHSPEC® Multi-Element Inner Single Optic Mounts are designed to mount a variety of optical components. The mounts support optical diameters from 5mm to 25.4mm, and edge thicknesses of 4mm to 17mm. With M29 x 0.75 outer diameter threads, these mounts can be easily positioned along the optical axis of our TECHSPEC® Multi-Element Outer Tubes. TECHSPEC® Multi-Element Inner Single Optic Mounts include one Delrin ring to ensure secure clamping force between the retainer ring and optic without damaging the optic.

**Note:** Our specially designed ME Spanner Wrench ([#13-567](#)) is highly recommended to move Inner Single Optic Mounts back and forth smoothly utilizing a combined metric and English graduated scale. The hollow design enables transmission of output beam while adjusting lens position. Non-scaled ME Spanner Wrench ([#11-046](#)) is also available.