

TECHSPEC<sup>®</sup> 5mm Diameter, C-Mount Thick Optic Mount



Stock #57-974 6 In Stock

-

1

+

£47<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £47.60 each                   |
| Qty 5-9        | £45.52 each                   |
| Qty 10-25      | £44.40 each                   |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

|                                   |                                           |
|-----------------------------------|-------------------------------------------|
| Fixed                             | Type:                                     |
| Circular                          | Type of Optics:                           |
| Optic Mount (Fixed)               | Function:                                 |
| Physical & Mechanical Properties  |                                           |
| 14.0                              | Extension Length (mm):                    |
| Black Anodized Aluminum (6061 T6) | Construction:                             |
| 18.0                              | Total Length (mm):                        |
| 30.0                              | Outer Diameter (mm):                      |
| 3.00                              | Clear Aperture CA (mm):                   |
| 6.5                               | Max. Thickness of Compatible Optics (mm): |
| 1.0                               | Min. Thickness of Compatible Optics (mm): |
| Threading & Mounting              |                                           |
| 5.0                               | Diameter of Compatible Optics (mm):       |
| C-Mount                           | Thread Type:                              |
| Regulatory Compliance             |                                           |
| Compliant                         | RoHS 2015:                                |
| View                              | Certificate of Conformance:               |
| Compliant                         | REACH 241:                                |

## PRODUCT DETAILS

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

**Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

## TECHNICAL INFORMATION

C-Thread Achromat / Thick Lens Mount

