

[See all 27 Products in Family](#)

## 6" x 6", Blue 470nm, UltraSeal Washdown Backlight

See More by [Advanced Illumination](#)



Advanced Illumination UltraSeal Washdown Backlights

Stock **#90-778** NEW **1 In Stock**

⊖ 1 ⊕ **£1,500<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	£1,500.00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

BL245-0606470ICSS **Model Number:**

50000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

**Note:**  
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination	<b>Manufacturer:</b>
Backlight	<b>Geometry:</b>
Constant	<b>Illumination Mode:</b>

## Physical & Mechanical Properties

173.0 x 173.0 x 24.0	<b>Dimensions (mm):</b>
698	<b>Weight (g):</b>
6 x 6	<b>Active Area (inches):</b>

## Optical Properties

Blue	<b>Color:</b>
470	<b>Wavelength (nm):</b>

## Electrical

1.08A	<b>Minimum Input Current:</b>
-------	-------------------------------

## Hardware & Interface Connectivity

Flying Leads	<b>Connector:</b>
24V	<b>Input Voltage (V):</b>

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#66-855](#)  
Europe: [#66-855](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#66-855](#)

## Environmental & Durability Factors

0 - 60	<b>Operating Temperature (°C):</b>
IP69K	<b>Environmental Rating:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- IP69K Certified for Extreme Washdown Environments
  - Stainless Steel Housing
  - Intensity Output up to 15,000 Lux
  - Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Advanced Illumination UltraSeal Washdown Backlights offer intense, even illumination up to 15,000 Lux while providing maximum protection in extreme environmental conditions. These IP69K certified backlights feature a crevice-free design to withstand high temperature washdown procedures and material buildup. The 316 stainless steel is FDA compliant, making them a suitable option for food or pharmaceutical inspection environments. Advanced Illumination UltraSeal Washdown Backlights are ideal for hygienic and aseptic manufacturing applications, such as prolonged liquid immersion and high-pressure steam cleaning common in food and beverage inspection and processing.
- Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.