

## 600 x 900mm, Metric Lab Table

See More by [TMC](#)



Stock #55-251 [CONTACT US](#)

⊖ 1 ⊕ £1,272<sup>00</sup>

[ADD TO CART](#)

### Volume Pricing

Qty 1+	£1,272.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Metric **Type:**

#### Physical & Mechanical Properties

50.00 **Thickness (mm):**

**Length (mm):**

900.00

**Width (mm):**

600.00

**Construction:**

Stainless Steel (400 Series) Top and Bottom Plates,  
Plated Steel Honeycomb Core, High Pressure  
Laminate Core Sidewalls

**Core Cell Area (cm<sup>2</sup>):**

≤3

**Flatness (mm):**

0.13

**Weight (kg):**

25.0

**Top Skin:**

430 Series Ferromagnetic Stainless Steel

**Core Density:**

13.3 lb/ft<sup>3</sup> (230 kg/m<sup>3</sup>)

**Core Cell Size:**

< 0.5 in.<sup>2</sup> (3 cm<sup>2</sup>)

**Core Shear Modulus:**

275,000 PSI (19300 kg/cm<sup>2</sup>)

**Top Skin Thickness:**

0.075 in. (2 mm)

## Threading & Mounting

**Mounting Threads:**

(748) M6 Tapped on 25mm Centerlines, on 37.5mm  
Corners

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

## Product Details

- Stainless Steel
- Economically Priced
- Lightweight Design

TMC™ CleanTop® Optical Honeycomb Breadboards are ultra-light (9 lbs/ft<sup>2</sup>, 44kg/m<sup>2</sup>) breadboards that employ countersunk, tapped holes in a thin top-skin of stainless steel. Top and bottom plates have a matte finish to lower reflectance and are ferromagnetic for mounting with magnetic bases. The tapped mounting holes allow for mounting with our English or Metric posts and post holders, as well as most commonly used optical mounts. TMC™ CleanTop® Optical Honeycomb Breadboards feature holes that are on 1" (25mm) centers with 1.5" (37.5mm) corners. Individually sealed holes allow for easy cleaning of spills

**Note:** Due to size and weight, shipping method and charges will differ from standard catalog charges; please contact our [Sales Department](#) for detailed information. Also note that these items will not be shipped overnight.