

# 8" x 10" Red Optical Cast Plastic Filter



Stock **#46-623** 5 In Stock

-

1

+

£132<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-49       | £132.00 each                  |
| Qty 50-99      | £118.40 each                  |
| Qty 100-249    | £106.40 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Color Filter

Physical & Mechanical Properties

Dimensions (mm):

203.2 x254.0

Length (mm):

254.00

|        |                             |
|--------|-----------------------------|
| 8 x 10 | Dimensions (inches):        |
| 1.50   | Thickness (mm):             |
| 203.20 | Width (mm):                 |
| ±0.3   | Dimensional Tolerance (mm): |

| Optical Properties     |                                        |
|------------------------|----------------------------------------|
| Thermoset ADC (CR-39®) | Substrate: <input type="checkbox"/>    |
| Uncoated               | Coating:                               |
| Red                    | Color:                                 |
| 1.501                  | Index of Refraction (n <sub>d</sub> ): |
| >20                    | Transmission (%):                      |
| 57.00                  | Abbe Number (v <sub>d</sub> ):         |

| Material Properties |                  |
|---------------------|------------------|
| 1.320 at 25°        | Density (g/cm³): |

| Environmental & Durability Factors |                             |
|------------------------------------|-----------------------------|
| 100 Continuous, 130 for 1 Hour     | Operating Temperature (°C): |


| Regulatory Compliance     |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 242:                  |

## Product Details

- Resistant to All Types of Chemicals and Solvents (Acetone, Acids, Alkali and Alcohols)
- Excellent Thermal Resistance
- Easily Drilled with High Speed Carbide Bits for Mounting

Optical Cast Plastic Color Filters have excellent thermal resistance. Traditionally, the limitations of plastic materials have made them unsuitable for demanding optical applications. However, advancement in plastic technology has produced filters with properties that can satisfy a variety of optical and environmental needs—and at half the weight of glass. Optical Cast Plastic Color Filters are ideal for use as environmental displays and filters. These filters, with their Thermoset ADC substrate, are also available in custom sizes, shapes, colors, and styles for qualified high volume OEM applications.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more

- High-precision surface quality and flatness
  - Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).