

[See all 78 Products in Family](#)

## Preloaded Norland Optical Adhesive NOA 61 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock #55-085 **10 In Stock**

⊖ 1 ⊕ £27<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-11	£27.20 each
Qty 12-19	£24.48 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

0.34 **Size (oz):**

61 **Norland Number:**

4 months **Shelf Life:**

**Type:**

Barrel

**Typical Applications:**

Preferred adhesive for precision optical bonding.  
Meets ML-A-3920. Low shrinkage and resiliency of adhesive minimizes strain

**Note:**

Contains 10g of adhesive

### Physical & Mechanical Properties

**Size (cc):**

10.00

### Optical Properties

**Index of Refraction (n<sub>d</sub>):**

1.56 @ 589nm

**Absorption Range (nm):**

320 - 380

### Material Properties

**Glass Bonding:**

Excellent

**Metal Bonding:**

Excellent

**Plastic Bonding:**

Fair

**Viscosity (cps):**

300

**Bonding Type:**

Glass to Glass/Metal

**Energy for Full Cure (J/cm<sup>2</sup>):**

3

### Environmental & Durability Factors

**Durability:**

Tough

### Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 253:**

[Compliant](#)

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as ML-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.