

[See all 13 Products in Family](#)

Lumenera INFINITY 8-20C Microscopy Color Camera

See More by [Teledyne Lumenera](#)



Stock #25-357 [CONTACT US](#)

- 1 + £3,400⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£3,400.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

Color **Spectrum:**

General

Color Microscopy Camera **Type:**

i8-LC00-20M **Model Number:**

Teledyne Lumenera **Manufacturer:**

INFINITY **Camera Series:**

Physical & Mechanical Properties

41.5 x 45 x 45 (includes lens mount) **Dimensions (mm):**

108 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1" **Sensor Format:**

20.00 **Resolution (Megapixels):**

19.00 **Frame Rate (fps):**

5,472 x 3,648 **Pixels (H x V):**

2.4 x 2.4 **Pixel Size, H x V (µm):**

13.13 x 8.76 **Sensing Area, H x V (mm):**

Sony IMX183 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

8/12 bit **Pixel Depth:**

73 **Dynamic Range (dB):**

Electrical

2.3 - 3.6 **Power Consumption (W):**

Hardware & Interface Connectivity

USB 3.1 **Interface:**

Power over USB **Power Supply:**

Not Specified **GPIOs:**

Hardware Trigger (GPIO) **Synchronization:**

Side Panel **Interface Port Orientation:**

9-pin Hirose (JST) **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

M3x0.5 (Integrated into Housing) **Mounting Threads:**

Environmental & Durability Factors

0 to +50 **Operating Temperature (°C):**

-30 to +70 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Exceptional Low Light Sensitivity
- Ideal for Life Sciences, Clinical, and Industrial Applications
- Affordable Price Point with Included Microscopy Software



Teledyne
Authorized
Distributor

Teledyne Lumenera INFINITY8 Microscopy Cameras offer an affordable solution for low light imaging in a compact form factor. Featuring low noise and large pixels, these cameras are ideal for a wide range of lighting conditions including the low light levels common in fluorescence imaging. Available with 1/1.8", 2/3", and 1" sensor sizes and megapixel range of 2 – 20 MP, each camera is compatible with Windows and Mac operating systems. Teledyne Lumenera INFINITY8 Microscopy Cameras include an INFINITY ANALYZE 7 software license, for camera operation and immediate analysis of the imaging results, and 3m Micro-B to Type-A USB cable.
