

TECHSPEC[®] Optical Component Kit



Stock #55-486 1 In Stock

-

1

+

£1,432^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	£1,432.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Optical Kit

Contents of Kit:

See Technical Information Tab

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ideal for Prototyping
- Matched to Mechanical Components
- Note: Potential change of packaging

Acomplete kit of precision optical components in stepped increments of focal length for systematic evaluation of optical system designs. Optics fit the mechanical components in the [C-Mount Component Kit](#) and can be found as individual components within our online catalog by following the links below.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Technical Information

List of Components	Quantity	Stock No.
Cylindrical Lens - 12.5mm Diameter x 12.5mm FL	1	#46-193
Cylindrical Lens - 12.5mm Diameter x 25mm FL	1	#46-194
Cylindrical Lens - 12.5mm Diameter x 50mm FL	1	#46-195
Cylindrical Lens - 25 x 50mm, 25mm FL	1	#46-020
Cylindrical Lens - 25 x 50mm, 50mm FL	1	#46-021
Aspheric Condenser - 12.7mm Diameter x 15mm FL	1	#43-370
Ball Lens - 3mm Diameter	1	#43-711
Ball Lens - 5mm Diameter	1	#43-712
Rod Lens - 3mm Diameter x 6mm L	1	#54-088
Rod Lens - 5mm Diameter x 10mm L	1	#54-090
Drum Lens - 2.4mm x 3.0mm	1	#45-549
GRIN Lens - 1.8mm Dia. x 0.0mm WD	1	#64-519
Right Angle Prism - 10mm	1	#32-330
Right Angle Prism - 20mm	1	#32-334
Silvered Corner Cube - 25.4mm Diameter	1	#45-187
Wedge Prism - 25mm Diameter	1	#45-557
Equilateral Prism - 15mm	1	#47-276
Dove Prism- 15mm x 64mm	1	#32-553
Cube Beamsplitter - 10mm Sq., 50R/50T	1	#32-601
Cube Beamsplitter - 20mm Sq., 50R/50T	1	#32-504
Plate Beamsplitter - 35mm Sq., 30R/70T	1	#45-324
Plate Beamsplitter - 35mm Sq., 70R/30T	1	#45-326
Broadband Hybrid Diffuser - 12.5mm Diameter	1	#36-610
Ground Glass Diffuser - 15mm Diameter	1	#45-652
First Surface Mirror - Protected Aluminum, 35mm Sq.	1	#45-519
First Surface Mirror - Protected Gold, 35mm Sq.	1	#45-520
Hexagonal Light Pipe - 4mm Aperture, 25mm Length High NA	1	#63-082