

TECHSPEC<sup>®</sup> T-Mount, 40mm Cube Mount, M6



12.5mm x 17.5mm Plate S-Mount Holder



Stock **#63-982** **3 In Stock**

-

1

+

£387<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | £387.20 each                  |
| Qty 5-9        | £341.84 each                  |
| Qty 10-25      | £314.72 each                  |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Optic Mount (Fixed)

Function:

Cube

Type of Optics:

|                                                                                 |  |
|---------------------------------------------------------------------------------|--|
| <b>Note:</b><br>Includes four T-Mount Aperture Caps ( <a href="#">#66-037</a> ) |  |
| <b>Dimensions of Compatible Optics (mm):</b><br>40.0 Sq.                        |  |
| <b>Physical &amp; Mechanical Properties</b>                                     |  |
| <b>Dimensions (mm):</b><br>54.5 x 54.5 x 63.8                                   |  |
| <b>Extension Length (mm):</b><br>54.5                                           |  |
| <b>Min. Thickness of Compatible Optics (mm):</b><br>40.0                        |  |
| <b>Max. Thickness of Compatible Optics (mm):</b><br>40.0                        |  |
| <b>Threading &amp; Mounting</b>                                                 |  |
| <b>Thread Type:</b><br>T-Mount                                                  |  |
| <b>Compatible Post:</b><br>M6 x 1.0                                             |  |
| <b>Regulatory Compliance</b>                                                    |  |
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>                                  |  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a>                      |  |
| <b>Reach 235:</b><br><a href="#">Compliant</a>                                  |  |

## Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
  - Provides a 90° Mounting Interface
  - ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.
- Note:** [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

## Technical Information

