

TECHSPEC® 0.179X, 35mm F-Mount TitanTL® Telecentric Lens



TitanTL® Telecentric Lens

Stock **#34-033** 3-4 DAYS

- 1 + **£9,413.75**

ADD TO CART

Qty 1+

£9,413.75

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Weight (kg):
10.04

Numerical Aperture NA, Object Side:
0.0056

Horizontal Field of View, 35mm Sensor:
201.6mm

Number of Elements (Groups):
7 (5)

Note:

TitanTL®
Type: Telecentric Lens
Primary Magnification PMAG: 0.179X
Maximum Sensor Format: 35mm
Working Distance (mm): 351
Mount: F-Mount
Aperture (f/#): f/16
Coating: λ/4 MgF ₂
Depth of Field (mm): ±25.0mm (20% @ 20 lp/mm, f/16)
FOV @ Max Sensor Format, H x V (mm): 201.6 x 134.4
Rear Filter Diameter (mm): 50.8
Typical Distortion @ 520nm (%): <0.2
Typical Telecentricity @ 520nm (°): <0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View