

TECHSPEC[®] 0.25X SilverTL™ Telecentric Lens



0.25X Magnification



Stock **#56-676** ☐ In Stock



1



£956.25

ADD TO CART

Qty 1+

£956.25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
158.00

Horizontal Field of View, 1/2" Sensor:
25.6mm

Filter Thread:
M46 x0.75 (Female)

Maximum Diameter (mm):

48.00
Weight (g): 266
Horizontal Field of View, 1/3" Sensor: 19.2mm
Numerical Aperture NA, Object Side: 0.021
Working Distance Tolerance (mm): ±3
Stock No. of Mounting Clamp: #56-870 Sold Separately
Resolution, Image Space MTF @ f/10: >40% @ 40 lp/mm
Number of Elements (Groups): 8 (5)
Note: SilverTL™
Typical Telecentricity @ 588nm (°): <0.035
Typical Distortion @ 588nm (%): <0.040
Type: Telecentric Lens
Primary Magnification PMAG: 0.25X
Maximum Sensor Format: 1/2"
Working Distance (mm): 160.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Construction: Anodized Aluminum
Depth of Field (mm): ±8.2 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 28.8 x 21.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View