

TECHSPEC[®] 0.30X SilverTL™ Telecentric Lens



0.30X Magnification



Stock **#58-428** ☐ In Stock

-

1

+

£956.25

ADD TO CART

Qty 1+

£956.25

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
158.00

Horizontal Field of View, 1/2" Sensor:
21.3mm

Filter Thread:
M43 x0.75 (Female)

Maximum Diameter (mm):

46.00
Weight (g): 291
Horizontal Field of View, 1/3" Sensor: 16mm
Numerical Aperture NA, Object Side: 0.025
Working Distance Tolerance (mm): ±3
Stock No. of Mounting Clamp: #56-870 Sold Separately
Resolution, Image Space MTF @ f/10: >40% @ 40 lp/mm
Number of Elements (Groups): 7 (6)
Note: SilverTL™
Typical Telecentricity @ 588nm (°): <0.025
Typical Distortion @ 588nm (%): <0.015
Type: Telecentric Lens
Primary Magnification PMAG: 0.3X
Maximum Sensor Format: 1/2"
Working Distance (mm): 139.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Construction: Anodized Aluminum
Depth of Field (mm): ±5.7 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 21.3 x 16.0
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View