

LightPath 355110 | 7.2mm Dia., 0.40 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-125** 3-4 DAYS

[Other Coating Options](#)



1



£80.75

ADD TO CART

Qty 1-10

£80.75

Qty 11+

£71.40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
7.20 ±0.020

Effective Focal Length EFL (mm):
6.24 @ 780nm

Numerical Aperture NA:

0.4
Substrate: D-ZLaF52LA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 780
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5
Edge Thickness ET (mm): 4.25
Center Thickness CT (mm): 5.16 ±0.05
f#: 1.25
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.28 (t) (mm) Material: BK7
Distance from Window to Lens (D) (mm): 2.682
Lightpath Lens Code: 355110
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 3.5
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant