

0.9 OD, 12.5mm Dia., IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock #12-008

3-4 DAYS



1



£174.25

ADD TO CART

Qty 1-10

£174.25

Qty 11+

£156.82

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50 ±0.2

Optical Density OD (Average):
0.9

Substrate: ☐
Germanium (Ge)

Coating: Metallic Based ND
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 12.6
Transmission Tolerance (%): ±1.5
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 2000 - 14,000
Parallelism (arcmin): <10
Clear Aperture (%): 90
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant