

Norland Optical Adhesive NOA 88, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA88, 1 oz. Application Bottle, #14-841

Stock **#14-841** ☒ In Stock

1 **£73.95**

ADD TO CART

Qty 1-4

£73.95

Qty 5+

£70.55

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
1

Glass Bonding:
Excellent

Metal Bonding:
Excellent

Plastic Bonding: Fair
Viscosity (cps): 250
Durability: Hard & Flexible
Index of Refraction n_d: 1.56 @ 589nm
Norland Number: 88
Shelf Life: 4 months
Type: Bottle
Typical Applications: Low outgassing and low viscosity for bonding glass or metal. Excellent transmission in the UV.
Absorption Range (nm): 315 - 395
Bonding Type: Glass to Glass/Metal
Energy for Full Cure (J/cm²): 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant