

10 x 10mm 600 Grit Ground Glass Diffuser



Stock **#38-783** 3-4 DAYS

- 1 + **£15.09**

ADD TO CART

Qty 1-10
£15.09
Qty 11+
£12.96
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating: Uncoated
Dimensional Tolerance (mm): ±0.76
Dimensions (mm): 10.00 x 10.00
Edges:

Cut Edges
Grit: 600
Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 10.00
Note: Sandblasted on first surface
Length (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant