

1000µm Aperture Diameter, 25mm Mounted, Acktar Blackened Pinhole

See More by [Acktar](#)



Acktar Blackened Pinholes (mounted)



Stock #12-175 3-4 DAYS



1



£122.40

ADD TO CART

Qty 1-9

£122.40

Qty 10+

£110.16

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Mounted

Outer Diameter (mm): 25.0 ±0.2
Construction: Stainless Steel
Fixed Aperture Diameter (µm): 1000 ±10
Diameter of Mount (mm): 25.0 ±0.2
Thickness (mm): 0.01 nominal
Coating: Magic Black™
Mount Thickness (mm): 3.0 ±0.1
Absorbance (%): 99
Model Number: PA-1-2-1000-25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant