

TECHSPEC[®] 1000nm, 12.5 x 17.6mm, Dichroic Longpass Filter



Stock #87-034 3-4 DAYS

-

1

+

£109.65

ADD TO CART

Qty 1-5

£109.65

Qty 6+

£87.55

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
12.5 x 17.6

Angle of Incidence (°):
45

Cut-On Wavelength (nm):
1,000.00

Substrate: Fused Silica (Coming 7980)
Length (mm): 17.60
Coating: Hard Coated
Reflection (%): >97, Average Polarization >95, Absolute Polarization
Reflection Wavelength (nm): 750 - 950
Surface Quality: 60-40
Thickness (mm): 1.05
Thickness Tolerance (mm): ±0.1
Transmission (%): >85, Average Polarization >80, Absolute Polarization
Transmission Wavelength (nm): 1035 - 1600
Type: Dichroic Filter
Width (mm): 12.50
Dimensional Tolerance (mm): +0.0/-0.2
Transmitted Wavefront Tolerance: λ/4
Cut-On Tolerance (%): ±2
Slope Factor (%): 3.00
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Wavelength Range (nm): 750 - 1600
Wavelength Range (μm): 0.75 - 1.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant