

101.6 x 127mm, 0° AOI, Hot Mirror



Hot Mirrors

Stock #43-453 3-4 DAYS

⊖ 1 ⊕ **£153.85**

ADD TO CART

Qty 1-9

£153.85

Qty 10+

£136.00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0.00

Coating:
Hot Mirror, 0°

Substrate:
BOROFLOAT®

Reflection (%):
>95, 750 - 1150nm

Dimensions (mm):
101.6 x 127.0

Surface Quality:
80-50

Thickness (mm):
3.30

Transmission (%):
>90, 425 - 675nm

Type:
Shortpass Filter

Dimensional Tolerance (mm):
±0.5

Coating Specification:
Surface 1: 0° Hot Mirror
Surface 2: None

Wavelength Range (nm):
425 - 1150

Surface Flatness (P-V):
4 - 6λ

Coating Type:
Dielectric

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)
