

TECHSPEC<sup>®</sup> 101.6 x 178.5mm EFL 45° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock #35-629 [CONTACT US](#)

[Other Coating Options](#)

-

1

+

£739.50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| £739.50                       |
| Qty 6+                        |
| £665.55                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:  
Off-Axis Parabolic Mirror

Diameter (mm):  
101.60 +0.00/-0.38

Effective Focal Length EFL (mm):

|                                                                                                                |
|----------------------------------------------------------------------------------------------------------------|
| 178.55                                                                                                         |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                       |
| <b>Radius of Curvature (mm):</b><br>304.80                                                                     |
| <b>Coating:</b><br>Protected Aluminum (400-2000nm)                                                             |
| <b>Coating Type:</b><br>Metal                                                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥85% @400 - 700nm<br>R <sub>avg</sub> ≥97% @2,000 - 12,000nm |
| <b>Off-Set Angle (°):</b><br>45                                                                                |
| <b>Parent Focal Length PFL (mm):</b><br>152.4                                                                  |
| <b>Surface Figure, RMS:</b><br>1λ                                                                              |
| <b>Surface Roughness (Angstroms):</b><br><100 RMS                                                              |
| <b>Wavelength Range (nm):</b><br>400 - 2000                                                                    |
| <b>Clear Aperture (%):</b><br>90                                                                               |
| <b>Surface Quality:</b><br>80-50                                                                               |
| <b>Compatible Mounting Plates:</b><br><a href="#">#83-977</a>                                                  |
| <b>Substrate:</b><br>Aluminum 6061-T6                                                                          |
| <b>Y Offset (mm):</b><br>126.25                                                                                |
| <b>Reflected Wavefront, RMS:</b><br>2λ                                                                         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |