


TECHSPEC® 1030nm, 25.4mm Dia., 45° Thin Film Polarizer



TECHSPEC® Ultrafast Thin Film Polarizers

Stock **#12-992** 3-4 DAYS

⊖ 1 ⊕ **£352.75**

ADD TO CART

Qty 1-4

£352.75

Qty 5+

£317.05

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45 ±1

Coating:
Thin Film Dielectric

Design Wavelength DWL (nm):
1030

Diameter (mm): 25.40 +0.00/-0.10
Extinction Ratio: 1000:1
Substrate: □ Fused Silica (Corning 7980)
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Linear Polarizer
Parallelism (arcmin): <3
Clear Aperture (%): 85
Transmitted Wavefront, P-V: λ/10 @ 633nm
Coating Specification: S1: R _s >99.8% @ 1030nm, T _p >98% @ 1030nm S2: R _p <0.1% @ 1030nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View