

TECHSPEC[®] 1064nm, 80R/20T, 25.4mm Dia., Nd:YAG Laser Output Coupler



TECHSPEC[®] Nd:YAG Laser Output Couplers

Stock #14-739 3-4 DAYS

⊖

1

⊕

£136.00

ADD TO CART

Qty 1-9

£136.00

Qty 10+

£119.85

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Output Coupler

Clear Aperture (%):
80

Coating Specification: S1: R_{avg} = 80±2% @ 1064nm Side 2: R_{avg} <0.2% @ 1064nm
Surface Flatness (P-V): λ/8
Coating Type: Dielectric
Coating: S1: Partially Reflective Laser Mirror (1064nm) S2: Laser V-Coat (1064nm)
Reflection/Transmission Ratio (R/T): 80/20
Design Wavelength DWL (nm): 1064
Diameter (mm): 25.40 +0.00/-0.10
Thickness (mm): 6.35 ±0.10
Angle of Incidence (°): 0
Substrate: Fused Silica (Corning 7980)
Note: Arrow on edge points towards S1
Parallelism (arcsec): <10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View