

1030nm CWL, 25mm Dia., OD 8 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock #15-401 3-4 DAYS

- 1 +

£2,681.75

ADD TO CART

Qty 1-9
£2,681.75
Qty 10+
£2,422.50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Angle of Incidence (°):

0
Optical Density OD (Average): 8.00
Clear Aperture CA (mm): 21.34
Center Wavelength CWL (nm): 1,031.20
Full Width-Half Max FWHM (nm): 0.60
Substrate:  BOROFLOAT®
Minimum Transmission (%): >85
Coating: Hard Coated
Transmission (%): T _{abs} >85% @ 1031.2nm
Type: Bandpass Filter
Blocking Wavelength Range (nm): 1042 - 1130, 940 - 1020
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 3.50 ±0.10
Note: Filter Design: Multi-Cavity
Substrate Thickness (mm): 2.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant