

TECHSPEC® 1064nm, 12.5mm Diameter, Raman Edge Filter



Stock **#86-232** ☐ In Stock

-

1

+

£429.25

ADD TO CART

Qty 1-9
£429.25

Qty 10+
£357.00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 1,074.60
Design Wavelength DWL (nm): 1064
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 831 - 1064
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <10.6
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >900
Coating Specification: T _{avg} ≥93% @ 1077.8 - 2000nm
Wavelength Range (nm): 831 - 1064
Laser Blocking Wavelength (nm): 1064.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View