

1064nm, 3-5mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal π Shaper_1064_Q-4

See More by [AdlOptica](#)



Focal Flat Top Beam Shaper



Stock #12-230

3-4 DAYS



1



£2,584.00

ADD TO CART

Qty 1-4

£2,584.00

Qty 5+

£2,323.90

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
20

Design Wavelength DWL (nm):
1064

Diameter (mm): 42.00
Model Number: πShaper_1064_Q-4
Length (mm): 29.00
Transmission (%): >99
Type: Beam Shaper
Weight (g): 50
Wavelength Range (nm): 1020 - 1100
Input Beam Diameter, 1/e² (mm): 3 - 5
Maximum Input Power, CW (kW): 0.15
Inner Thread: M30 x0.75
Outer Thread: M30 x0.75
Compatible Adapter: #12-322
Input Beam Mode: TEM ₀₀
Typical Input Beam Mode Quality, M²: <1.5
Input Beam Divergence (mrad): ±20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
