

TECHSPEC® 1.0mm Dia. x 0.6mm FL, VIS-EXT Coated Plano-Convex Lens



Stock **#35-694** 3-4 DAYS

[Other Coating Options](#)

- 1 + **£67.15**

ADD TO CART

Qty 1-9
£67.15
Qty 10+
£60.35
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
1.00 +0.0/-0.025

Effective Focal Length EFL (mm):

0.60 @ 587.6nm
Back Focal Length BFL (mm): 0.17
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-LASF9
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 0.80 ±0.05
Edge Thickness ET (mm): 0.39
Radius R₁ (mm): 0.51
Clear Aperture CA (mm): 0.5
f/#: 0.6
Numerical Aperture NA: 0.83
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant