

TECHSPEC® 10mm Dia., 1mm Thick, MgF₂ AR Coated Sapphire Window



Stock **#36-201** 3-4 DAYS

- 1 + **£51.42**

ADD TO CART

Qty 1-24
£51.42
Qty 25+
£41.23
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%): ≥90
Clear Aperture CA (mm): 9.00
Diameter (mm): 10.00 ±0.25
Thickness (mm): 1.00 ±0.15
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8
Density (g/cm³): 3.97
Edges: Fine Ground
Index of Refraction n_d: 1.77
Knoop Hardness (kg/mm²): 1900
Parallelism (arcmin): ≤3.5
Poisson's Ratio: 0.27
Substrate: Sapphire (Al ₂ O ₃)
Surface Flatness (P-V): 2λ (typical)
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 435

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant