


TECHSPEC® 12.5mm 1064nm, Laser Line Non-Polarizing Beamsplitter



Laser Line Non-Polarizing Cube Beamsplitters



Stock **#35-965** ☒ In Stock

⊖ 1 ⊕

£215.05

ADD TO CART

Qty 1-5
£215.05
Qty 6+
£172.13
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
±2

Bevel:
Protective as needed

Clear Aperture (%) : 90
Coating Specification : <0.25% Reflection on Entrance and Exit Faces
Construction : Cube
Design Wavelength DWL (nm) : 1064
Dimensions (mm) : 12.5 x 12.5 x 12.5 ±0.1
Reflection/Transmission Tolerance (%) : ±5
Substrate : ☐ N-BK7
Surface Flatness (P-V) : λ/8
Surface Quality : 40-20
Transmission (%) : <45% ±5% @ DWL
Type : Non-Polarizing Beamsplitter
 Ts-Tp : <3% @ DWL
Power (fringes) @ 632.8nm : 1.50
Irregularity (fringes) @ 632.8nm : 0.25

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View