

TECHSPEC® 10mm VIS, 30R/70T, Non-Polarizing Cube Beamsplitter



Stock #13-417 3-4 DAYS

- 1 + **£192.95**

ADD TO CART

Qty 1-5
£192.95

Qty 6+
£150.45

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VS
Coating Specification: R_{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 10.0 x 10.0 x 10.0 ±0.1
Reflection/Transmission Ratio (R/T): 30/70
Substrate: □ N-BK7
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
[Ts-Tp]: <6%
Absolute Transmission (%): 65 ±10
Average Transmission (%): 65 ±5
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View