

## 12" x 6" Laser Safety Barrier



Laser Safety Barriers

Stock **#14-731** 3-4 DAYS

- 1 + **£60.77**

ADD TO CART

|               |
|---------------|
| Qty 1-3       |
| <b>£60.77</b> |

|               |
|---------------|
| Qty 4+        |
| <b>£53.55</b> |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

**Construction:**  
Bead-Blasted Anodized Aluminum

**Dimensions (inches):**  
6 x 6

**Dimensions (mm):**  
304.8 x 152.4

|                                                                                                                                                                                                                                                                      |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Thickness (mm):</b><br>2.00                                                                                                                                                                                                                                       |
| <b>Through Hole Length (mm):</b><br>50.80                                                                                                                                                                                                                            |
| <b>Included Hardware:</b> <ul style="list-style-type: none"><li>· (2) ¼-20, 1/2" Long SHCS</li><li>· (2) M6 x 1.0, 10mm Long SHCS</li><li>· (1) English Allen Wrench (<a href="#">#55-192</a>)</li><li>· (1) Metric Allen Wrench (<a href="#">#55-200</a>)</li></ul> |
| <b>Style:</b><br>Straight Wall                                                                                                                                                                                                                                       |
| <b>Through Hole Orientation:</b><br>3 x Holes Centered on Mounting Lip                                                                                                                                                                                               |
| <b>Through Hole Diameter (mm):</b><br>7                                                                                                                                                                                                                              |
| <b>Base Width (mm):</b><br>20                                                                                                                                                                                                                                        |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |