

Richardson Gratings™ 1200 Grooves, 12.5 x 25mm, 250nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock **#15-762** 3-4 DAYS

-

1

+

£129.20

ADD TO CART

Qty 1+

£129.20

Volume Pricing

[Request Quote](#)

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):

175 - 400
Blaze Wavelength (nm): 250 ±25
Blaze Angle (°): 8.6
Peak Efficiency, Typical (%): 62
Dimensions (mm): 12.5 x 25.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.50
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S, P and Average
Master Reference: 2840
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View